product data sheet

item no. 81.000.6331.0

switched-mode power supply WIPOS PB1 5-3

wipos switched-mode power supply, nominal voltage: 5 V DC / 3A, (setting range 5,0-5,5 V DC) sustained short-circuit protection, input voltage range: 90-264 V AC / 120-375V DC, single phase, DIN rail mounted device 2 mod



item no.	81.000.6331.0
EAN	4049088106149
order unit	1 piece(s)

certificates / approvals

technical data

general

connection type	screw connection
number of phases	single phase power supply
suitable for modular version	yes
mounting type, other	no
mounting type, wall mounting	no
rail mounting possible	yes
housing material	plastic
operating temperature min.	-40 °C
operating temperature max.	71 °C
relative humidity min.	20 %
relative humidity max.	95 %
storage temperature / transport min.	85 °C
storage temperature / transport max.	-40 °C
degree of protection (IP)	IP20
pollution degree	2
parallel-service possible	no

technical data

function display	DC OK LED grün (U(o) 3.5...4.5V)
function display "DC Low"	DC LOW LED rot (U(o) < 3.5...4.5V)
short-circuit protective device	current limiting (hiccup mode)
temperature coefficient	±0,03%/K
ripple and noise	< 0.05 V
hold time 115V AC	> 20 ms
hold time 230V AC	> 100 ms

isolating voltage Output DC	4242 V
cohesive resistance (In-/Output)	100 MOhm
derating	61°C...71°C: 2.5 %/K
cooling	free convection
MTBF	832,000h
connector cross section (input	min. 0.5mm² (AWG24), max. 2.5mm² (AWG12)
connector cross section (output)	min. 0.5mm² (AWG24), max. 2.5mm² (AWG12)
wire strip length	7 mm
permissible torque max.	0.6 Nm
control "Adj"	trimming potentiometer for fine-tuning of U(out)
CE-Norm	EN61000-6-3, EN 55022 Class B,EN61000-3-2, EN61000-3-3, EN61000-6-2,EN55024, EN61000-4-2, Level 4,EN61000-4-3 Level 3, EN61000-4-4 Level 4,EN61000-4-5 L-N Level 3, L/N-FG Level 4,EN61000-4-6 Level 3, EN61000-4-8 Level 4,EN61000-4-11, ENV 50204 Level 2,EN61204-3
approval UL	UL 508 Listed, UL60950-1 Recognized
number of +	2
number of -	2
further terminals	L, N

output

type of output voltage	DC
power output	15 W
output voltage stabilized	yes
output voltage	5 V
min. output voltage	5 V
max. output voltage	5.5 V
min. output voltage	5 V
max. output voltage	5.5 V
output current	3 A


input

type of voltage (input voltage)	
primary voltage range	90 V
min. input voltage	90 V
max. input voltage	264 V
rated frequency min.	47 Hz
rated frequency max.	63 Hz
max. starting current	40 A
input fuse	T2A / 250V (internal)
input protection	varistor (voltage-sensitive resistor)

dimensions

depth	56.5 mm
width	35 mm
height	91 mm
mounting distance horizontal	25 mm
mounting distance vertical	25 mm
weight	130 g

technical drawing



Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.

Qu - PEE 12/92

Teile-Nr. / Part-No.	Typ / Type
81.000.6310.0	wipos PB1 24-1
81.000.6322.0	wipos PB1 12-2
81.000.6331.0	wipos PB1 5-3

Weitere Angaben siehe KATALOG oder eKatalog.
Additional data see CATALOG or eCatalog.

www.wieland-electric.com
eshop.wieland-electric.com

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten.
Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance	CAD-Zeichnung, keine manuellen Änderungen CAD-Drawing, no manual modifications allowed	1. Verwendung: First Use:	Blatt: Sheet:

Werkstoff/ Material	2016	Tag/ Date	Name	Zeichnung Nr./ Drawing No.
Maßstab/Scale	gezeichnet drawn	29.02.	Koetzner	T 81.000.6310.0 01K
	geprüft checked			Maße in mm/Dimensions are in mm
	Normgepr. Stand. check			

Datei/ File: 031501__01K.DCD

Ersatz für/ Replacement for:

Index | Datum/ Blatt Date/ Sheet

Änderung/ Revision

wieland
www.wieland-electric.com

Type

Benennung/ Title: Teilespezifikation / Component specification

Schaltnetzteil / Switching Power Supply

81__000__6310__001K__2 CADW3072 Koetzner 2016-03-07T11:16:00 1.000