product data sheet

item no. 81.000.6142.0

switched-mode power supply WIPOS P1 12-10

wipos switched-mode power supply, nominal voltage: 12 V DC / 10A (setting range 11,4-14,5 V DC), sustained short-circuit protection, input voltage range: 115 V AC / 230 V AC, 210-370 V DC, single phase, W x H x D: 63,2 × 123,6 × 123,6 mm



item no.	81.000.6142.0
EAN	4049088106118
order unit	1 piece(s)

certificates / approvals

technical data

general

connection type	screw connection
number of phases	single phase power supply
suitable for modular version	yes
mounting type, other	no
mounting type, wall mounting	no
rail mounting possible	yes
housing material	metal
operating temperature min.	-35 °C
operating temperature max.	71 °C
relative humidity min.	20 %
relative humidity max.	95 %
storage temperature / transport min.	85 °C
storage temperature / transport max.	-35 °C
degree of protection (IP)	IP20
parallel-service possible	yes
number of parallel switchable device	3

technical data

function display	"DC OK" (LED green) (U(o) 17.6...19.4V)
function display "DC Low"	"DC Low" (LED red)
short-circuit protective device	current limitation (fold forward)
temperature coefficient	±0,03%/K
ripple and noise	< 0.05 V
hold time 115V AC	> 25 ms
hold time 230V AC	> 30 ms

isolating voltage Output DC	4242 V
cohesive resistance (In-/Output)	100 MOhm
derating	61°C...71°C: 2.5 %/K
cooling	free convection
MTBF	450,000h
connector cross section (input	min. 0.5mm² (AWG24)max. 6mm² (AWG10)
connector cross section (output)	min. 0.5mm² (AWG24)max. 6mm² (AWG10)
wire strip length	8 mm
permissible torque max.	0.6 Nm
CE-Norm	EN55022 & EN61000-6-3, EN61000-3-2,EN61000-3-3, EN55024 & EN61000-6-2,EN61000-4-2, EN61000-4-3, EN61000-4-4,EN61000-4-5, EN61000-4-6, EN61000-4-8,EN61000-4-11, EN60204-1, EN61204-3
TÜV/safety	EN60950-1, EN61558-1, EN61558-2-16(comply with EN60204) , IRAM
approval UL	UL 508 Listed, UL60950-1 Recognized
number of +	2
number of -	2
further terminals	L1, N, PE, NC (not used)

output

type of output voltage	DC
power output	120 W
output voltage stabilized	yes
output voltage	12 V
min. output voltage	11.4 V
max. output voltage	14.5 V
min. output voltage	11.4 V
max. output voltage	14.5 V
output current	10 A


input

type of voltage (input voltage)	
primary voltage range	90 V
min. input voltage	90 V
max. input voltage	264 V
rated frequency min.	47 Hz
rated frequency max.	63 Hz
input fuse	T3,15A / 250V (internal)

dimensions

depth	123.6 m
width	63.2 mm
height	123.6 mm
mounting distance horizontal	25 mm
mounting distance vertical	25 mm
weight	920 g

technical drawing



Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.

Qu - PEE 12/92

Weitere Angaben siehe KATALOG oder eKatalog. Additional data see CATALOG or eCatalog.	www.wieland-electric.com eshop.wieland-electric.com

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten.
Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance	CAD-Zeichnung, keine manuellen Änderungen CAD-Drawing, no manual modifications allowed	1. Verwendung: First Use:	Blatt: Sheet:

Maßstab/Scale	Werkstoff/ Material	2016	Tag/ Date	Name
		gezeichnet drawn	04.03.	Koetzner
		geprüft checked		
		Normgepr. Stand. check		

Zeichnung Nr./ Drawing No.
81.000.6142.0 01K
Maße in mm/Dimensions are in mm

Datei/ File: 033791__01K.DCD
Ersatz für/ Replacement for:

Index / Änderung/ Revision	Datum/ Blatt Date/ Sheet	
wieland www.wieland-electric.com	Type	Benennung/ Title: Teilespezifikation / Component specification Schaltnetzteil / Switching Power Supply wipos P1 12 VDC / 10 A 1PH

81__000__6142__001K__2 CADW3072 Koetzner 2016-03-07T11:22:26 1.000