


product data sheet

item no. 56.706.5055.6


feed-through terminal WKFN 6 D1/2/35 BLAU

Feed-through terminal with tension spring connection for mounting on TS35/ TS 32, nominal cross section: 6 mm², width: 8 mm, color: blue



item no.	56.706.5055.6
EAN	4015573911123
order unit	50 piece(s)

certificates / approvals



technical data

general

nominal cross section	6 mm ²
color	blue
number of levels	1
number of clamp positions per level	3
width/grid dimension	8 mm
insulating housing	PA666
flammability class of insulation material acc. with UL94	V0
explosion-tested version "Ex e"	yes
mounting method	DIN rail (top hat rail)/G-rail
terminal blocks for electrical installations	yes
Anzahl der Klemmstellen je Etage	3
Montageart	DIN rail (top hat rail)/G-rail
Brennbarkeitsklasse des Isolierstoffs	V0
Reihenklemmen für Installationsverteiler	yes

technical data

rated current	41 A
rated voltage	800 V
rated impulse voltage	8 kV
pollution degree	3
closing plate required	yes
type of insulation material	thermoplastic
length	89.9 mm

connection data

connection type 1	spring clamp connection
-------------------	-------------------------

connection type 2	spring clamp connection
minimum cross section solid	0.2 mm ²
maximum cross section solid	10 mm ²
minimum cross section fine stranded	0.2 mm ²
maximum cross section fine stranded	6 mm ²
wire strip length	12 mm

technical data UL/CSA

cross section UL	24-8 AWG
voltage UL	600 V
current factory wiring	50 A
current field wiring	50 A
cross section CSA	24-8 AWG
voltage CSA	600 V
current CSA	41 A

accessories

item no.	type	description
Z7.282.5227.0	insulated jumper bar IVB WKFN 6- 2	INSUL. JUMPER BAR IVB WKFN 6 - 2
Z7.282.5327.0	insulated jumper bar IVB WKFN 6- 3	INSUL. JUMPER BAR IVB WKFN 6 - 3
Z7.282.5427.0	insulated jumper bar IVB WKFN 6- 4	INSUL. JUMPER BAR IVB WKFN 6 - 4
Z7.282.5527.0	insulated jumper bar IVB WKFN 6- 5	INSUL. JUMPER BAR IVB WKFN 6 - 5
98.300.0000.0	mounting rail TS 35x7,5 UNPERF - l:2000mm	Mounting rail TS 35, unslotted, size 7,5 mm, length 2 m, material steel. galv. zinc-plated and passivated
98.300.1000.0	mounting rail TS 35x7,5 PERF 15mm - l:2000mm	Mounting rail TS 35, slotted, size 7,5 mm, length 2 m, material steel. galv. zinc-plated and passivated
98.300.1800.0	mounting rail TS 35x7,5 PERF 18mm - l:2000mm	Mounting rail TS 35, slotted, size 7,5 mm, length 2 m, material steel. galv. zinc-plated and passivated
98.300.1900.0	mounting rail TS 35x7,5 PERF 25mm - l:2000mm	Mounting rail TS 35, slotted, size 7,5 mm, length 2 m, material steel. galv. zinc-plated and passivated
98.360.0000.0	mounting rail TS 35x15-2,3 UNPERF - l:2000mm	Mounting rail TS 35, unslotted, size 15 mm, length 2 m, material steel. galv. zinc-plated and passivated
98.360.0004.0	mounting rail TS 35x15-2,3 UNPERF FZN - l:2000mm	Mounting rail TS 35, unslotted, size 15 mm, length 2 m, material steel, hot galvanized
98.370.0000.0	mounting rail TS 35x15 UNPERF - l:2000mm	Mounting rail TS 35, unslotted, size 15 mm, length 2 m, material steel. galv. zinc-plated and dichromated
98.370.1000.0	mounting rail TS 35x15 PERF 15mm - l:2000mm	Mounting rail TS 35, slotted, size 15 mm, length 2 m, material steel. galv. zinc-plated and passivated
98.380.0000.0	mounting rail TS 35x15-2,3 UNPERF CU - l:2000mm	Mounting rail TS 35, unslotted, size 15 mm, length 2 m, material E copper
07.313.0655.0	end plate APFN 6 D1/2/35	End plate for DIN rail terminal blocks type WKFN 6 D1/2..., color: grey
07.313.0655.6	end plate APFN 6 D1/2/35 BLAU	End plate for DIN rail terminal blocks type WKFN 6 D1/2..., color: blue
07.313.0655.7	end plate APFN 6 D1/2/35 GRUEN	End plate for DIN rail terminal blocks type WKFN 6 D1/2..., color: green
07.313.0755.0	partition TWFN 6 D1/2/35	Partition for DIN rail terminal blocks type WKFN 6 D1/2..., color: grey
07.313.0755.6	partition TWFN 6 D1/2/35 BLAU	Partition for DIN rail terminal blocks type TWFN 6 D1/2/35 BLUE
04.242.8053.0	marking tag strips 9705 A / 8 / 10	Marking tag strips for DIN rail terminal blocks type 9700 A / 8..., 10 tags per strip, color: blue, unmarked, markable with Wieplot plotter-system

