


product data sheet

item no. 56.716.9053.0

earth terminal WKF 16SL/35

Ground terminal with tension spring connection for mounting on TS 35, nominal cross section: 16 mm², width: 12 mm, color: Green-yellow



item no.	56.716.9053.0
EAN	4015573501805
order unit	50 piece(s)

certificates / approvals



technical data

general

nominal cross section	16 mm²
color	green/yellow
number of levels	1
number of clamp positions per level	2
width/grid dimension	12 mm
insulating housing	PA666
flammability class of insulation material acc. with UL94	V0
explosion-tested version "Ex e"	yes
mounting method	DIN rail (top hat rail) 35/7.5 mm
terminal blocks for electrical installations	yes
Anzahl der Klemmstellen je Etage	2
Montageart	DIN rail (top hat rail) 35/7.5 mm
Brennbarkeitsklasse des Isolierstoffs	V0
Reihenklemmen für Installationsverteiler	yes

technical data

rated impulse voltage	8 kV
pollution degree	3
closing plate required	no
type of insulation material	thermoplastic
length	82 mm

connection data

connection type 1	spring clamp connection
connection type 2	spring clamp connection
minimum cross section solid	4 mm²


maximum cross section solid	10 mm ²
minimum cross section fine stranded	4 mm ²
maximum cross section fine stranded	16 mm ²
minimum cross section stranded	16 mm ²
maximum cross section stranded	16 mm ²
wire strip length	15 mm

technical data UL/CSA


cross section UL	24-4 AWG
cross section CSA	12-4 AWG

accessories


item no.	type	description
Z7.284.4227.0	jumper bar IVBWK 16- 2	Cross connector, insulated for DIN rail terminal blocks type WK F..., 2 -pole
98.300.0000.0	mounting rail TS 35x7,5 UNPERF - l:2000mm	Mounting rail TS 35, unslotted, size 7,5 mm, length 2 m, material steel. galv. zinc-plated and passivated
98.300.1000.0	mounting rail TS 35x7,5 PERF 15mm - l:2000mm	Mounting rail TS 35, slotted, size 7,5 mm, length 2 m, material steel. galv. zinc-plated and passivated
98.300.1800.0	mounting rail TS 35x7,5 PERF 18mm - l:2000mm	Mounting rail TS 35, slotted, size 7,5 mm, length 2 m, material steel. galv. zinc-plated and passivated
98.300.1900.0	mounting rail TS 35x7,5 PERF 25mm - l:2000mm	Mounting rail TS 35, slotted, size 7,5 mm, length 2 m, material steel. galv. zinc-plated and passivated
98.360.0000.0	mounting rail TS 35x15-2,3 UNPERF - l:2000mm	Mounting rail TS 35, unslotted, size 15 mm, length 2 m, material steel. galv. zinc-plated and passivated
98.360.0004.0	mounting rail TS 35x15-2,3 UNPERF FZN - l:2000mm	Mounting rail TS 35, unslotted, size 15 mm, length 2 m, material steel, hot galvanized
98.370.0000.0	mounting rail TS 35x15 UNPERF - l:2000mm	Mounting rail TS 35, unslotted, size 15 mm, length 2 m, material steel. galv. zinc-plated and dichromated
98.370.1000.0	mounting rail TS 35x15 PERF 15mm - l:2000mm	Mounting rail TS 35, slotted, size 15 mm, length 2 m, material steel. galv. zinc-plated and passivated
98.380.0000.0	mounting rail TS 35x15-2,3 UNPERF CU - l:2000mm	Mounting rail TS 35, unslotted, size 15 mm, length 2 m, material E copper
04.242.6053.0	marking tag strips 9705 A / 6 / 10	Marking tag strips for DIN rail terminal blocks type 9700 A / 6..., 10 tags per strip, color: white, unmarked, markable with Wieplot plotter- system



Ansicht ohne Isolierplatte
view without insulating cover



Hutschiene EN 60715-35x7,5
mounting rail EN 60715-35x7,5
Hutschiene EN 60715-35x15
mounting rail EN 60715-35x15



Isolierplatte (Farbe: gelb)
insulating cover (colour: yellow)

Weitere Daten siehe Katalog
further datas see catalog

Freitoleranz nach DIN		CAD - Zeichnung, keine manuellen Änderungen			I,Verwendung: -		Bl.: 1 von 1	
	/	Maßstab	Werkstoff und Oberfläche:		2002	Tag	Name	Index
	/		Farbe: grün		Entworfen	13.11.	Schneiderb.	
	/		colour: green		Geprüft		-	
	/				Normgepr.	-	-	
	/				Ersatz für: -			
a	22.06.2010/				Typ		Benennung	
Buchstabe	Datum / Blatt				WKf 16 SL/		SCHUTZLEITERKLEMME	
Änderung					35		earth lead terminal (screwless)	
							schraubenlos	