
product data sheet

item no. 56.735.0053.6

feed-through terminal WKF 35/35 BLAU

Feed-through terminal with tension spring connection for mounting on TS35, nominal cross section: 35 mm², width: 16 mm, color: blue



item no.	56.735.0053.6
EAN	4015573732223
order unit	10 piece(s)

certificates / approvals

technical data

general

nominal cross section	35 mm²
color	blue
number of levels	1
number of clamp positions per level	2
width/grid dimension	16 mm
insulating housing	PA666
inflammability class of insulation material acc. with UL94	V0
explosion-tested version "Ex e"	yes
mounting method	DIN rail (top hat rail) 35/7.5 mm
terminal blocks for electrical installations	no
Anzahl der Klemmstellen je Etage	2
Montageart	DIN rail (top hat rail) 35/7.5 mm
Brennbarkeitsklasse des Isolierstoffs	V0
Reihenklemmen für Installationsverteiler	no

technical data

rated current	125 A
rated voltage	800 V
rated impulse voltage	8 kV
pollution degree	3
closing plate required	no
type of insulation material	thermoplastic
length	99.9 mm

connection data

connection type 1	spring clamp connection

connection type 2	spring clamp connection
minimum cross section solid	2.5 mm²
maximum cross section solid	10 mm²
minimum cross section fine stranded	2.5 mm²
maximum cross section fine stranded	35 mm²
minimum cross section stranded	16 mm²
maximum cross section stranded	35 mm²
wire strip length	25 mm


technical data UL/CSA

cross section UL	12-2 AWG
voltage UL	600 V
current factory wiring	120 A
current field wiring	120 A
cross section CSA	12-2 AWG
voltage CSA	600 V
current CSA	120 A

accessories

item no.	type	description
Z7.285.6227.0	jumper bar IVB WKF 35-2	Cross connector, insulated for DIN rail terminal blocks type WKF..., 2 -pole
98.300.0000.0	mounting rail TS 35x7,5 UNPERF - l:2000mm	Mounting rail TS 35, unslotted, size 7,5 mm, length 2 m, material steel. galv. zinc-plated and passivated
98.300.1000.0	mounting rail TS 35x7,5 PERF 15mm - l:2000mm	Mounting rail TS 35, slotted, size 7,5 mm, length 2 m, material steel. galv. zinc-plated and passivated
98.300.1800.0	mounting rail TS 35x7,5 PERF 18mm - l:2000mm	Mounting rail TS 35, slotted, size 7,5 mm, length 2 m, material steel. galv. zinc-plated and passivated
98.300.1900.0	mounting rail TS 35x7,5 PERF 25mm - l:2000mm	Mounting rail TS 35, slotted, size 7,5 mm, length 2 m, material steel. galv. zinc-plated and passivated
98.360.0000.0	mounting rail TS 35x15-2,3 UNPERF - l:2000mm	Mounting rail TS 35, unslotted, size 15 mm, length 2 m, material steel. galv. zinc-plated and passivated
98.360.0004.0	mounting rail TS 35x15-2,3 UNPERF FZN - l:2000mm	Mounting rail TS 35, unslotted, size 15 mm, length 2 m, material steel, hot galvanized
98.370.0000.0	mounting rail TS 35x15 UNPERF - l:2000mm	Mounting rail TS 35, unslotted, size 15 mm, length 2 m, material steel. galv. zinc-plated and dichromated
98.370.1000.0	mounting rail TS 35x15 PERF 15mm - l:2000mm	Mounting rail TS 35, slotted, size 15 mm, length 2 m, material steel. galv. zinc-plated and passivated
98.380.0000.0	mounting rail TS 35x15-2,3 UNPERF CU - l:2000mm	Mounting rail TS 35, unslotted, size 15 mm, length 2 m, material E copper
04.343.9253.8	warning cover ADF 35/5	Cover with warning symbol for DIN rail terminal blocks type WKF ...
04.242.8053.0	marking tag strips 9705 A / 8 / 10	Marking tag strips for DIN rail terminal blocks type 9700 A / 8…, 10 tags per strip, color: blue, unmarked, markable with Wieplot plotter-system

technical drawing



Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.

These dimensions will be especially checked at delivery
Only inspection dimensions
With /E marked dimensions are only valid for internal use

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig

Technische Daten
/technical Data

	VDE	UL	CSA
Bemessungsspannung V /rated voltage	800	600	600
Bemessungsstrom A /rated current	125	115	115
Anschlussbereich max. mm²/AWG /connection range	35	2	2
Bemessungsquerschnitt 35mm² /rated cross-section 35mm²			
Brennbarkeitsklasse UL 94 V-0 /flamability rating UL 94 V-0			
Verschmutzungsgrad 3/Überspannungskategorie III /pollution deggree 3/overvoltage category III			

Weitere Daten siehe KATALOG oder eKatalog | www.wieland-electric.com
additional data see CATALOG or eCATALOG | eshop.wieland-electric.com

Teile-Nr. /part number	Typ / type	Farbe / colour
56.735.0053.0	WKF 35/35	kieselgrau, ähnl. RAL 7032 / silicic gray, similar RAL 7032
56.735.0053.6	WKF 35/35 blau	lichtblau, ähnl. RAL 5012 / light blue, similar RAL 5012

Tolerierung Size ISO 14405 Ⓔ / Tolerance system Size ISO 14405 Ⓔ.
(This ISO-standard describes the envolope principle. According to the envolope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten
Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1. Verwendung: First Use:

Blatt: 1 von 1
Sheet: 1 of 1

Werkstoff / Material: PA 6.6

Maßstab / Scale: 2:1

Vol. mm³ Ofl./Srf. mm²

	Tag/Date	Name
gezeichnet drawn	26.02.2004	Postler F.

Elektronische Freigabe
Electronic Release

Zeichnung Nr. / Drawing No.: T 56.735.0053.0 01K

Index: a

Maße in mm / Dimensions are in mm

Ersatz für / Replacement for:

Index	Datum / Blatt Date / Sheet	Änderung / Revision
a	01.02.2022 /	

wieland

Type

Benennung/Title

DURCHGANGSKLEMME

through terminal

Federkraftanschluss / spring clamp connection

2023-02-10 10:25:18 1.000

01-QU-RD-32/21