



QQGQ2.E197597

Power Supplies, Information Technology Equipment Including Electrical Business Equipment - Component

Page Bottom

Power Supplies, Information Technology Equipment Including Electrical Business Equipment - Component

See General Information for Power Supplies, Information Technology Equipment Including Electrical Business Equipment - Component

WIELAND ELECTRIC GMBH

E197597

BRENNERSTRASSE 10-14

96052 BAMBERG, GERMANY

	Rated Input			Max Output							
Model No.	Volts	Hz	SC	V	A	VA	OC	SP	EP	FC	GC
WIPOS 24VDC/1,15A 1PH V											
	105-250ac	47-63	0	24	1.15	38	0	1950	-	0	0
WIPOS 24VDC/1,25A 1PH V											
	105-250ac	47-63	0	24	1.15	38	0	1950	-	0	0
WIPOS 24VDC/10A 1PH H											
	105-125/ 210-250ac	47-63	0	27	10	240	0	1950	-	0	0
WIPOS 24VDC/10A 1PH V[*r]											
	115/ 230ac	47-63	0	30dc	10	300	3	60950	-	5	0
WIPOS 24VDC/2,5A 1PH H											
	105-250ac	47-63	0	27	2.5	60	0	1950	-	0	0
WIPOS 24VDC/20A 1PH H											
	210-250ac	47-63	0	27	20	480	0	1950	-	0	0
WIPOS 24VDC/20A 3PH H											
	360-500ac	47-63	0	27	40	1014	0	1950	-	0	0
WIPOS 24VDC/40A 3PH H											
	360-500ac	47-63	0	27	40	1014	0	1950	-	0	0
WIPOS 24VDC/5,0A 1PH H											
	115/ 230ac	47-63	0	23.5	6.4	150	3	1950	20B	3,4	1
WIPOS P1 24-1.25[*r]											
	120-240ac	47-63	0	24dc	-	30	3	60950-1	20B	0	1
WIPOS P1 24-10											
	115/ 230ac	47-63	0	24dc	14.5	308.1	3	60950-1	20B	0	1
WIPOS P1 24-2.5											
	100-240ac	47-63	0	28.5dc	3.48	91.45	3	60950-1	20B	0	1

WIPOS P1 24-20											
	115/ 230ac	47-63	0	24.07dc	27.3	567.1	3	60950-1	20B	0	0
WIPOS P1 24-3.8											
	115/ 220/ 230ac	47-63	0	24.07	7.6	131.7	3	60950-1	20B	0	1
WIPOS P1 24-5											
	115/ 220/ 230ac	47-63	0	24.07	7.6	131.7	3	60950-1	20B	0	1
WIPOS P3 24-10											
	3PH 400-500Vac	47-63	0	24.1dc	13.7	289.92	3	60950-1	20B	0	1
WIPOS P3 24-20											
	3PH 400-500ac	47-63	0	24.1	29.6	513	3	60950-1	20B	0	1
WIPOS P3 24-40											
	3PH 400-500Vac	47-63	0	24.1dc	44.5	1038	3	60950-1	20B	0	1
WIPOS P3 24-5											
	3PH 400-500Vac	47-63	0	24.08dc	6.95	152.32	-	60950-1	20B	0	1
WIPOS PS1 1.25											
	100-240Vac; 90-350Vdc	-	0	5dc	5.0	25.0	3	60950-1, 2nd Ed + AM1	20B	0	1
				12dc	2.5	30.0	3				
				24dc	1.3	31.2	3				
WIPOS PS1 2.5											
	100-240Vac/ 90-350Vdc	50/60	0	12dc	4.5	54	3	60950-1, 2nd Ed + AM1	20B	5	1
				24dc	2.5	60	3				
WIPOS PS1 24-20[*r]											
	100-240Vac; 90-350Vdc	50/60	0	24dc	20	480	3	60950-1, 2nd Ed + AM1	20B	8	1
				48dc	10	480	3				
				29.6dc	26.37	605.9	3				
				57.68dc	13.1	619.9	3				
WIPOS PS1 24-5											
	100-240Vac; 90-350Vdc	50/60	0	24dc	5	120	3	60950-1, 2nd Ed + AM1	20B	0	1
				29.21dc	8.32	150.1	3				
WIPOS PS3 24-10											
	3AC380-480Vac/ 2AC380-480Vac/ 450-600Vdc	50/60	0	24dc	10	240	3	60950-1, 2nd Ed + AM1	20B	5	1
WIPOS PS3 24-20[*r]											
	3ac 380-480 or 2ac 380-480 or 450-600Vdc	50/60	0	24dc	20	480	3	60950-1, 2nd Ed + AM1	20B	5	1

[illegible]

	115/ 220/ 230ac	47-63	0	12.02dc	14	124.68	3	60950-1	20B	0	1
wipos P1 15-0.34[*r]											
	100-240ac	47-63	0	15dc	-	5	3	60950-1	20B	0	1
wipos P1 15-0.34-B[*r]											
	100-240ac	47-63	0	15dc	-	5	3	60950-1	20B	0	1
wipos P1 15-0.67[*r]											
	100-240ac	47-63	0	15dc	-	10	3	60950-1	20B	1	0
wipos P1 15-0.67-B[*r]											
	100-240ac	47-63	0	15dc	-	10	3	60950-1	20B	1	0
wipos P1 15-1.2[*r]											
	100-240ac	47-63	0	15dc	-	18	3	60950-1	20B	1	0
wipos P1 15-1.2-B[*r]											
	100-240ac	47-63	0	15dc	-	18	3	60950-1	20B	1	0
wipos P1 24-0.21[*r]											
	100-240ac	47-63	0	24dc	-	5	3	60950-1	20B	0	1
wipos P1 24-0.21-B[*r]											
	100-240ac	47-63	0	24dc	-	5	3	60950-1	20B	0	1
wipos P1 24-0.42[*r]											
	100-240ac	47-63	0	24dc	-	10	3	60950-1	20B	1	0
wipos P1 24-0.42-B[*r]											
	100-240ac	47-63	0	24dc	-	10	3	60950-1	20B	1	0
wipos P1 24-0.75[*r]											
	100-240ac	47-63	0	24dc	-	18	3	60950-1	20B	1	0
wipos P1 24-0.75-B[*r]											
	100-240ac	47-63	0	24dc	-	18	3	60950-1	20B	1	0
wipos P1 24-1.1-UPS[*r]											
	120-240ac	47-63	0	24dc	-	30	3	60950-1	20B	0	1
wipos P1 24-1.25-B[*r]											
	120-240ac	47-63	0	24dc	-	30	3	60950-1	20B	0	1
wipos P1 24-10-A											
	115/ 230ac	47-63	0	47.9dc	8	286.7	3	60950-1	20B	0	1
wipos P1 24-12.5[*r]											
	115/ 230ac	47-63	0	24dc	12.5	300	3	60950-1	20B	0	1
wipos P1 24-12.5-A[*r]											
	115/ 230ac	47-63	0	24dc	12.5	300	3	60950-1	20B	0	1
wipos P1 24-17.6-UPS											
	115-230ac	47-63	0	24.07dc	27.3	567.1	3	60950-1	20B	0	1
wipos P1 24-2.2-UPS											
	100-240ac	47-63	0	28.5dc	3.48	91.45	3	60950-1	20B	0	1

wipos P1 24-2.5-B[*r]											
	100-240ac	47-63	0	27.7	25	60	1	1950	20B	0	1
wipos P1 24-20-A											
	115-230ac	47-63	0	24.07dc	27.3	567.1	3	60950-1	20B	0	1
wipos P1 24-3.8-A											
	115/ 220/ 230ac	47-63	0	24.07dc	7.6	131.7	3	60950-1	20B	0	1
wipos P1 24-3.8-L[*r]											
	100-240ac	47-63	0	24	-	100	3	60950-1	20B	0	1
wipos P1 24-4.2[*r]											
	100-240ac	47-63	0	24	-	100	3	60950-1	20B	0	1
wipos P1 24-4.4-UPS											
	115/ 220/ 230ac	47-63	0	24.07dc	7.6	131.7	3	60950-1	20B	0	1
wipos P1 24-5-A											
	115/ 220/ 230ac	47-63	0	24.07dc	7.6	131.7	3	60950-1	20B	0	1
wipos P1 24-8.8-UPS											
	115/ 230ac	47-63	0	24dc	14.5	308.1	3	60950-1	20B	0	1
wipos P1 48-0.55-UPS											
	100-240ac	47-63	0	56.87dc	0.93	42	3	60950-1	20B	0	1
wipos P1 48-0.625											
	100-240ac	47-63	0	56.87dc	0.93	42	3	60950-1	20B	0	1
wipos P1 48-0.625-B											
	100-240ac	47-63	0	56.87dc	0.93	42	3	60950-1	20B	0	1
wipos P1 48-1.1-UPS											
	100-240ac	47-63	0	57.0dc	1.8	91	3	60950-1	20B	0	1
wipos P1 48-1.25											
	100-240ac	47-63	0	55.94	1.45	69.6	1	1950	20B	0	1
wipos P1 48-1.25-B											
	100-240ac	47-63	0	55.94	1.45	69.6	1	1950	20B	0	1
wipos P1 48-10											
	115-230ac	47-63	0	48.05dc	13.5	583.9	3	60950-1	20B	0	1
wipos P1 48-10-A											
	115-230ac	47-63	0	48.05dc	13.5	583.9	3	60950-1	20B	0	1
wipos P1 48-2.1											
	100-240ac	47-63	0	48.13	5.5	134.56	3	60950-1	20B	0	1
wipos P1 48-2.2-UPS											
	115/ 220/ 230ac	47-63	0	47.89dc	3.8	150.08	3	60950-1	20B	0	1
wipos P1 48-2.5											

[illegible]

	400-500ac	47-63	0	12.05	11.2	115.73	3	60950-1, 2nd	20B	0	1
wipos P2 24-4.2[*r]											
	400-500ac	47-63	0	24	4.2	-	3	60950-1, 2nd	20B	0	1
wipos P2 48-2.1											
	400-500ac	47-63	0	48.1	10.2	118.63	3	60950-1, 2nd	20B	0	1
wipos P3 12-10											
	3PH 400-500ac	47/63	0	12.08dc	14.8	142.76	3	60950-1	20B	0	1
wipos P3 24-40-L											
	3PH 400-500Vac	47-63	0	24.1dc	44.5	1038	3	60950-1	20B	0	1
wipos P3 48-10											
	3PH 400-500ac	47-63	0	42.8dc	19.7	498	3	60950-1	20B	1	0
wipos P3 48-20											
	3PH 400-500Vac	47-63	0	48.1dc	27.5	1176	3	60950-1	20B	0	1
wipos P3 48-5											
	3PH 400-500Vac	47-63	0	48.03dc	6.32	279.93	3	60950-1	20B	0	1
wipos PB1 12-0.83[*r]											
	100-240ac	47-63	0	12	-	10	3	60950-1	20B	0	2
wipos PB1 12-2[*r]											
	100-240ac	47-63	0	12	2	-	3	60950-1, 2nd	20B	0	2
wipos PB1 12-2.75[*r]											
	100-240ac	47-63	0	12	-	33	3	60950-1	20B	0	2
wipos PB1 12-4.5[*r]											
	100-240ac	47-63	0	12	-	54	3	60950-1	20B	0	2
wipos PB1 12-6[*r]											
	100-240ac	47-63	0	12	-	72	3	60950-1	20B	0	2
wipos PB1 15-0.67[*r]											
	100-240ac	47-63	0	15	-	10	3	60950-1	20B	0	2
wipos PB1 15-1.6[*r]											
	100-240ac	47-63	0	15	1.6	-	3	60950-1, 2nd	20B	0	2
wipos PB1 15-2.4[*r]											
	100-240ac	47-63	0	15	-	36	3	60950-1	20B	0	2
wipos PB1 15-4[*r]											
	100-240ac	47-63	0	15	-	60	3	60950-1	20B	0	2
wipos PB1 15-5[*r]											
	100-240ac	47-63	0	15	-	75	3	60950-1	20B	0	2
wipos PB1 24-0.42[*r]											
	100-240ac	47-63	0	24	-	10	3	60950-1	20B	0	2
wipos PB1 24-1											
	100-240ac	47-63	0	24.0	1.3	31.2	3	60950-1, 2nd	20B	0	2
wipos PB1 24-1.5[*r]											
	100-240ac	47-63	0	24	-	36	3	60950-1	20B	0	2

wipos PB1 24-2.5[*r]											
	100-240ac	47-63	0	24	-	60	3	60950-1	20B	0	2
wipos PB1 24-3.8[*r]											
	100-240ac	47-63	0	24	-	91	3	60950-1	20B	0	2
wipos PB1 24-4.2[*r]											
	100-240ac	47-63	0	24	-	100	3	60950-1	20B	0	2
wipos PB1 5-1.5[*r]											
	100-240ac	47-63	0	5	-	7.5	3	60950-1	20B	0	2
wipos PB1 5-12[*r]											
	100-240ac	47-63	0	5	-	60	3	60950-1	20B	0	2
wipos PB1 5-3											
	100-240ac	47-63	0	5.1	4.3	21.3	3	60950-1, 2nd	20B	0	2
wipos PB1 5-4.5[*r]											
	100-240ac	47-63	0	5	-	22.5	3	60950-1	20B	0	2
wipos PB1 5-7[*r]											
	100-240ac	47-63	0	5	-	35	3	60950-1	20B	0	2
wipos R20[*r]											
	21-28dc	-	3	28	20	-	3	60950-1	-	3	0

[*r] - Output values are rated.

Marking: Company name and model designation on the product or on the smallest unit container in which the product is packaged.

Last Updated on 2014-09-12

[Questions?](#)

[Print this page](#)

[Terms of Use](#)

[Page Top](#)

© 2014 UL LLC

When the UL Leaf Mark is on the product, or when the word "Environment" is included in the UL Mark, please search the [UL Environment database](#) for additional information regarding this product's certification.

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2014 UL LLC".