


product data sheet

item no. 05.560.3419.0

mounting sheet Podis LED

Fixture plate for easy mounting inside of mesh cable trays with grid measures 50 x 100 mm; safe assembly without loose parts (screws, nuts, revets,...); stainless steel



item no.	05.560.3419.0
EAN	4049088312069
order unit	50 piece(s)

certificates / approvals

technical data

general

material	stainless steel
----------	-----------------

dimensions

length	154 mm
assembly width	105 mm

assembly

item no.	type	description
83.240.0030.0	Luminaire RST 24V DC 5W	podis® LED Luminaire, lamp power 4.9 W, 24 V DC, 450 lm, power supply system RST20i3 signal brown, IP65, protection class II, color housing light grey
83.240.0031.1	Luminaire RST 24V DC 5W 1S	podis® LED Luminaire, with through-wiring, lamp power 4.9 W, 24 V DC, 450 lm, power supply system RST20i3 signal brown, IP65, protection class II, color housing black
83.242.0040.0	Luminaire RST 120VDC 5W STD	podis® LED Luminaire, lamp power 5 W, 120 V DC, 450 lm, power supply system RST16i3 leaves green, IP65, protection class II, color housing black
83.243.0030.0	Luminaire RST 230V AC 2x3W 1U	podis® LED Luminaire, with through-wiring, lamp power 6 W, 230 V AC, 500 lm, power supply system RST20i3 black, IP65, protection class II, color housing black
83.240.0030.9	Luminaire LED RST 24V DC GN	energy saving LED-luminaire, green; pluggable by round connectors RST 20i2, opposite configuration, brown coding; for harsh industrial environments (e.g. wind turbines) and emergency light acc. EN 60598-2-22; typ. 290 lm; 15...32 V DC; 5 W; green (525 nm); integrated reverse polarity-, overload- and shortage protection; IP68/IP69K encapsulation; operating temperature -40...+70 °C (- 40...160 °F); EN 60598-1
83.240.0050.0	Luminaire MIN 24V DC 5W	energy saving LED-luminaire pluggable by revos MINI Q5; for harsh industrial environments (e.g. wind turbines) and emergency light acc. EN 60598-2-22; typ. 360 lm; 15...32 V DC; 5 W; daytime white, 6500 K; integrated reverse polarity-, overload- and shortage protection; IP 65 encapsulation; operating temperature -40...+70 °C (-40...160 °F); DIN 60598- 1; cURus
83.241.0040.0	Luminaire RST 70-250V AC 5W	energy saving LED-luminaire pluggable by round connectors RST 20i3, opposite configuration, black coding; for harsh industrial environments (e.g. wind turbines) and emergency light acc. EN 60598-2-22; orientation independent mounting; 70...250 V AC; 5 W; typ. 360 lm; daytime white, 6500 K; ; Schutzart IP65 operating temperature -40...+55 °C (-40...130 ° F); EN 60598-1
83.243.0040.0	Luminaire LED RST 230V AC 2x3W	
83.240.1030.0	Luminaire RST 24V DC 5W LS	energy saving LED-luminaire with integrated optic pluggable by round connectors RST 20i2, opposite configuration, brown coding; optimized for long rooms, such as towers, shafts, corridors, tunnels, especially as emergency light acc. EN 60598-2-22; typ. 450 lm; 15...32 V

	DC; 5 W; daytime white, 6500 K; integrated reverse polarity-, overload- and shortage protection; Schutzart IP65 operating temperature -40...+70 ° C (-40...160 ° F); DIN 60598-1; cURus
--	--