product data sheet

item no. 83.040.1334.0

IP switch WIENET LMS 16-W

wienet IP switch. 16 Fast Ethernet ports with Auto MDI/MDI-X, Communication with SCADA software via Modbus-TCP, Communication with NMS (Network management system) via SNMP, Port-based QoS for deterministic data transmission, EMS level 3 protection for extreme outdoor environments, IEEE 802.3az Energy Efficient Ethernet (EEE), Jumbo Frame Support (Up to 2048 Bytes), Supports 10/100 Mbps Auto-Negotiation, Metal housing, Redundant 8,4 V … 52,8 V DC power input and P-Fail relay, Wide operating temperature range from -40°C to 75°C (-40°F ... 167°F)



item no.	83.040.1334.0
EAN	4049088371189
order unit	1 piece(s)

certificates / approvals

c UL us LISTED

technical data

mounting method	DIN rail (top hat rail)
degree of protection (IP)	IP30
housing material	metal
manageable	no
ethernet	yes
power over Ethernet	no
Fast Ethernet	yes
Gigabit Ethernet	no
number of ports 10/100 Mbps RJ45	16
diagnostic LEDs	power/link status/data/data rate
10 gigabit Ethernet	no
number of ports 10/100/1000 Mbps RJ45	0
number of ports 100 Mbps SC	0
number of 100 Mbps ST-Ports	0

technical data

voltage type	DC
min. operating temperature	-40 °C
max. operation temperature	75 °C
redundant power supply	2 power inputs

supply circuit

voltage type	DC
operating voltage min.	9 V
operating voltage max.	30 V
power consumption max.	< 8 W


dimensions

depth	84 mm
width	74 mm
height	120 mm

accessories

item no.	type	description
78.999.4000.0	patch-cables MOD ZBH RJ45 0,25 m	
78.999.4100.0	patch-cables MOD ZBH RJ45 0,5 m	
78.999.4200.0	patch-cables MOD ZBH RJ45 1,0 m	
78.999.4300.0	patch-cables MOD ZBH RJ45 2,0 m	
78.999.4400.0	patch-cables MOD ZBH RJ45 3,0 m	
78.999.4500.0	patch-cables MOD ZBH RJ45 5,0 m	
78.999.4600.0	patch-cables MOD ZBH RJ45 7,5 m	
78.999.4700.0	patch-cables MOD ZBH RJ45 10 m	

technical drawing



Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.

Qu - PEE 12/92

A 1 2 3 4 5 6 7 8 9 10 11 12 13 14 15 16 17 18 19 20 M1 M2 M3 L G i 11.1 12.1 1.1

Weitere Angaben siehe KATALOG oder eKatalog. Additional data see CATALOG or eCatalog.	www.wieland-electric.com eshop.wieland-electric.com

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten.
Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance	CAD-Zeichnung, keine manuellen Änderungen CAD-Drawing, no manual modifications allowed	1. Verwendung: First Use:	Blatt: Sheet:

Werkstoff/ Material	2016	Tag/ Date	Name
Maßstab/Scale	gezeichnet drawn	28.09.	Koetzner
	geprüft checked		
	Normgepr. Stand. check		

Zeichnung Nr./ Drawing No.
83.040.1334.0 01K
Maße in mm/Dimensions are in mm

Datei/ File: 044621__01K.DCD
Ersatz für/ Replacement for:

Index | Datum/ Blatt Date/ Sheet
Änderung/ Revision

wieland
www.wieland-electric.com

Type

Benennung/ Title
Teilespezifikation / Component specification
IP-SWITCH / IP SWITCH
wienet LMS 16-W

83_040__1334__001K__2 CADW3072 Koetzner 2016-09-28T08:42:30 1.000