product data sheet

item no. G5.936.3042.3

distributor MST20I5V 2P1M15 30 WSC3

METALYNX² T-distributor, rated voltage 250 V, rated current 20 A, number of poles 3, degree of protection (ip) IP20, number of inputs 1, number of outputs 2, pole codification L, N, PE, mechanical coding code 3, color of coding/ contact carrier white, ral number coding/contact insert 9016, halogen free yes, housing material polyamide, with mounting option, Flex Drop, fire load 2.054 kWh/ St, contact material CuZn, surface finish silver-plated, pollution degree 2, rated impulse voltage 4 kV

item no.	G5.936.3042.3
EAN	4049088280702
order unit	10 piece(s)

certificates / approvals

technical data

general

rated current	20 A
rated voltage	250 V
rated impulse voltage	4 kV
pollution degree	2
mechanical coding	code 3
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	white
Pole codification	L, N, PE
RAL number coding/contact insert	9016

lead

model	T-distributor
microfuse (6,3x25 mm)	
drop	sheathed cable LSOH
no. of poles on drop	3
cross section of drop	1.5 mm²
termination of drop	free end
length of drop	3 m
lenght of open end	3 m
stripping length of drop	10 mm
design of conductor ends	ultrasonically compressed wire ends
color of the coding pin	white (C3)
wiring system	
internal cross secction	

model

number of inputs	1
number of outputs	2
type of fastening	yes
degree of protection (IP)	IP20
type of distributor	T-distributor

material

housing material	polyamide

halogen free	yes
contact material	CuZn
fire load	2.054 kWh/St
insulation components continous temperature	100 °C
surface finish	silver-plated