product data sheet

item no. G5.800.0044.6

distributor MST20I6V 3P1 40 GRC6

METALYNX² switch module, rated voltage 250 V, rated current 20 A, number of poles 6, degree of protection (ip) IP20, number of inputs 1, number of outputs 3, pole codification 1, 2, 3, 4, N, PE, mechanical coding code 6, color of coding/ contact carrier grey, halogen free yes, housing material polyamide, parallel connection, with fastening option, fire load 1.641 kWh/St, contact material CuZn, surface finish silver-plated, pollution degree 2, rated impulse voltage 4 kV, length 162 mm, height 38.4 mm, width 150.6 mm

item no.	G5.800.0044.6
EAN	4049088233135
order unit	16 piece(s)

certificates / approvals

c UL us LISTED

technical data

general

rated current	20 A
rated voltage	250 V
rated impulse voltage	4 kV
pollution degree	2
mechanical coding	code 6
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	grey
Pole codification	1, 2, 3, 4, N, PE

lead

model	H-Distributor with switching functionality
microfuse (6,3x25 mm)	
drop	
no. of poles on drop	6
cross section of drop	
termination of drop	
length of drop	
lenght of open end	
stripping length of drop	
design of conductor ends	
color of the coding pin	grey (C6)
wiring system	On/Off
internal cross secction	2.5 mm²

model

number of inputs	1
number of outputs	3
type of fastening	yes
degree of protection (IP)	IP20
type of distributor	switch module

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	1.641 kWh/St
insulation components continous temperature	100 °C
surface finish	silver-plated

dimensions

length	162 mm
width	150.6 mm
height	38.4 mm