

product data sheet

item no. G5.961.1592.8

distributor MST20I4V 2P1C15 15 SWC8

METALYNX² T-distributor, rated voltage 250 V, rated current 20 A, number of poles 6, degree of protection (ip) IP20, number of inputs 1, number of outputs 2, pole codification 1, 2, 3, 4, N, PE, mechanical coding code 8, color of coding/ contact carrier black, ral number coding/contact insert 9005, halogen free yes, housing material polyamide, parallel connection, with fastening option, fire load 0 kWh/St, contact material CuZn, surface finish silver-plated, pollution degree 2, rated impulse voltage 4 kV

item no.	G5.961.1592.8
EAN	4049088281341
order unit	20 piece(s)

certificates / approvals

technical data

general

rated current	20 A
rated voltage	250 V
rated impulse voltage	4 kV
pollution degree	2
mechanical coding	code 8
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	black
Pole codification	1, 2, 3, 4, N, PE
RAL number coding/contact insert	9005

lead

model	T-distributor
microfuse (6,3x25 mm)	
drop	metal conduit 16 mm
no. of poles on drop	6
cross section of drop	1.5 mm ²
termination of drop	free end
length of drop	1.5 m
length of open end	1.5 m
stripping length of drop	10 mm
design of conductor ends	
color of the coding pin	black (C8)
wiring system	
internal cross section	

model

number of inputs	1
number of outputs	2
type of fastening	yes
degree of protection (IP)	IP20
type of distributor	T-distributor

material

housing material	polyamide
------------------	-----------

halogen free	yes
contact material	CuZn
fire load	0 kWh/St
insulation components continous temperature	100 °C
surface finish	silver-plated