

product data sheet

item no. G5.931.0596.1

distributor MST20I3V 2P1C60 05 BLC1

METALYNX² T-distributor, rated voltage 250 V, rated current 32 A, number of poles 3, degree of protection (ip) IP20, number of inputs 1, number of outputs 2, pole codification L, N, PE, mechanical coding code 1, color of coding/ contact carrier blue, halogen free yes, housing material polyamide, with mounting option, Conduit Drop, fire load 1.09 kWh/St, contact material CuZn, surface finish silver-plated, pollution degree 2, rated impulse voltage 4 kV

item no.	G5.931.0596.1
EAN	4049088279911
order unit	30 piece(s)

certificates / approvals

technical data

general

rated current	32 A
rated voltage	250 V
rated impulse voltage	4 kV
pollution degree	2
mechanical coding	code 1
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	blue
Pole codification	L, N, PE

lead

model	T-distributor
microfuse (6,3x25 mm)	
drop	metal conduit 16 mm
no. of poles on drop	3
cross section of drop	6 mm ²
termination of drop	free end
length of drop	0.5 m
length of open end	0.5 m
stripping length of drop	10 mm
design of conductor ends	
color of the coding pin	sky blue (C1)
wiring system	
internal cross section	

model

number of inputs	1
number of outputs	2
type of fastening	yes
degree of protection (IP)	IP20
type of distributor	T-distributor

material

housing material	polyamide
halogen free	yes
contact material	CuZn

fire load	1.09 kWh/St
insulation components continous temperature	100 °C
surface finish	silver-plated