product data sheet

item no. 92.257.4000.7

cable assembly GST18I5KSBS 15 40GN04

gesis® CLASSIC connecting cable, female - male, number of poles 5, rated voltage 250 V / 400 V, rated current 16 A, cable type H05VV-F, fire class Eca, total length 4 m, nominal cross section conductor 1.5 mm², color of coding/ contact carrier may green



item no.	92.257.4000.7
EAN	4049088290657
order unit	10 piece(s)

certificates / approvals

technical data

general

rated current	16 A
rated voltage	250 V / 400 V
rated impulse voltage	4 kV
pollution degree	2
mechanical coding	code 4
continuity resistor	46.4 mOhm
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	may green
Pole codification	1, 2, PE, 3/N, 4
color of housing inclusive strain relief	black

model

nominal cross section conductor	1.5 mm²
degree of protection (IP)	IP40
cable type	H05VV-F
cable color	black
cable diameter max.	10.1 mm
version of cable	female - male
type of cord set	connecting cable
version cable end 1	GST18i5 female
version cable end 2	GST18i5 plug

material

surface finish	tin-plated
halogen free	no
continuous temperature of cable	70 °C

insulation components continous temperature	100 °C
fire load	2.688 kWh/St
fire class	Eca


dimensions

total length	4 m

accessories

item no.	type	description
05.587.3156.0	lock (G)ST18 WS	Locking device for cable to cable connection GST18i3-5, white
05.587.3156.1	lock (G)ST18 SW	Locking device for cable to cable connection GST18i3-5, black
05.564.5353.0	cover cap GST18I3/4/5 SW	Cover piece 12 pole black for female parts GST18i3-6
05.564.5353.2	cover cap GST18I3/4/5 WS	Cover piece 12 pole white for female parts GST18i3-6
05.566.9253.0	cover cap GST18I5 BUCHSEN	Cover for female connectors GST18i5, black
05.583.1853.0	cover cap GST18I5 STECKER	

technical drawing



These dimensions will be especially checked at delivery
Only inspection dimensions
With /E marked dimensions are only valid for internal use

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patenterteilung oder Gebrauchsmuster-Eintragung vorbehalten.
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.

Teile-Nr. part-no.	L	Beispiel (Farbe: maigrün) exampel (colour: may green)	Typ type
92.257.XX00.7	XX in dm-Schritten	92.257.1000.7 = 10dm/L= 1000mm	GST1815KSBS 15 10GN04
U2.257.XX00.7	XX in m-Schritten	U2.257.1200.7 = 12 m/L=12000mm	GST1815KSBS 15 X12GN04

Weitere Daten siehe KATALOG oder eKatalog.
Additional data see CATALOG or eCatalog.

www.wieland-electric.com
eshop.wieland-electric.com

Toleranz System ISO 14405Ⓔ/Tolerance system Size ISO 14405Ⓔ.
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten.
Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach
General tolerance

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1.Verwendung:
First Use: -

Blatt: 1 von 1
Sheet: 1 of 1

Werkstoff/Material

Maßstab/Scale: x

	Name	Tag/Date
2014		
gezeichnet drawn	Dütsch T.	19.11.
geprüft checked	-	-
Normgepr. Stand. check	-	-

Zeichnung Nr./Drawing No.: T 92.257.0500.7 01K
Index

Vol. mm³ Ofl./Surf. mm²

Maße in mm/Dimensions are in mm

Ersatz für/Replacement for: -

Index | Datum / Blatt Date / Sheet
Änderung/Revision

wieland
www.wieland-electric.com

Type: GST1815 KSBS 15 ..GN04

Benennung/Title: KONFEKT_LEITUNG
Buchse/female - Stecker/male
Schraubanschluß/screw connection 250/400V 1,5qmm

922570500701K_2 CADW3027 Duetsch 2014-11-20T11:32:53 21.000

QU-MEE-01/14 -