product data sheet

item no. 92.754.7453.0

connector GST18I5S S1PZR1 S MPB02

gesis® CLASSIC connector, pre-assembled, number of poles 5, male, connection type screw connection, rated voltage 250 V / 400 V, rated current 20 A, cable diameter 7 - 12 mm, color of coding/ contact carrier pastel blue



item no.	92.754.7453.0
EAN	4049088318849
order unit	50 piece(s)

certificates / approvals

technical data

general

rated current	20 A
rated voltage	250 V / 400 V
rated impulse voltage	4 kV
strain relief	yes
pollution degree	2
mechanical coding	code 2
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	pastel blue
Pole codification	L, N, PE, D1, D2
color of housing inclusive strain relief	black
RAL-Nummer Codierung/Kontakteinsatz	5024

connection data

cable diameter max.	12 mm
cable diameter min.	7 mm
connection cross section solid mm² max.	2.5 mm²
connection cross section solid mm² min.	0.5 mm²
connection cross section fine stranded mm² max.	2.5 mm²
connection cross section fine stranded mm² min.	0.5 mm²
terminations per pole	1
sheath strip length	37 mm
wire strip length	7 mm

model

model	male
connection type	screw connection
degree of protection (IP)	IP40

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	0.168 kWh/St
insulation components continous temperature	100 °C
surface finish	tin-plated

dimensions

length	76.4 mm
width	47.75 mm
height	17.2 mm

accessories

item no.	type	description
05.587.3156.0	lock (G)ST18 WS	Locking device for cable to cable connection GST18i3-5, white
05.587.3156.1	lock (G)ST18 SW	Locking device for cable to cable connection GST18i3-5, black
05.564.5353.0	cover cap GST18I3/4/5 SW	Cover piece 12 pole black for female parts GST18i3-6
05.564.5353.2	cover cap GST18I3/4/5 WS	Cover piece 12 pole white for female parts GST18i3-6
05.566.9253.0	cover cap GST18I5 BUCHSEN	Cover for female connectors GST18i5, black

assembly

item no.	type	description
92.753.7453.0	connector GST18I5S B1PZR1 S MPB02	gesis® CLASSIC connector, pre-assembled, number of poles 5, female, connection type screw connection, rated voltage 250 V / 400 V, rated current 20 A, cable diameter 7 - 12 mm, color of coding/ contact carrier pastel blue
92.053.0058.0	device connector GST18I5L B1H WS	gesis® CLASSIC device connector, solder connector, horizontal, without fastening flange, number of poles 5, model female, connection type soldering connection, rated voltage 250 V / 400 V, rated current 20 A, color of coding/ contact carrier white, degree of protection (ip) IP20, built-in component soldering connection, angle of plug square, pole codification 3, N, PE, 2, 1, mechanical coding code 1, housing material polyamide, halogen free yes, fire load 0.047 kWh/ St, contact material CuZn, surface finish tin-plated, pollution degree 2, rated impulse voltage 4 kV, length 24 mm, height 13 mm, width 47.7 mm
92.053.0258.0	device connector GST18I5L B1V BL01	gesis® CLASSIC device connector, solder connector, horizontal, without fastening flange, number of poles 5, model female, connection type soldering connection, rated voltage 50 V, rated current 6 A, color of coding/ contact carrier light blue, degree of protection (ip) IP20, built-in component soldering connection, angle of plug square, pole codification 1, 2, 3, 4, 5, mechanical coding code 6, housing material polyamide, halogen free yes, fire load 0.055 kWh/ St, contact material CuZn, surface finish tin-plated, pollution degree 2, rated impulse voltage 4 kV, length 24 mm, height 13 mm, width 47.7 mm
92.053.0458.0	device connector GST18I5L B1H PB02	gesis® CLASSIC device connector, solder connector, horizontal, without fastening flange, number of poles 5, model female, connection type soldering connection, rated voltage 250 V / 400 V, rated current 20 A, color of coding/ contact carrier pastel blue, degree of protection (ip) IP20, built-in component soldering connection, angle of plug square, pole codification L, N, PE, D1, D2, mechanical coding code 2, housing material polyamide, halogen free yes, fire load 0.047 kWh/St, contact material CuZn, surface finish tin-plated, pollution degree 2, rated impulse voltage 4 kV, length 24 mm, height 13 mm, width 47.7 mm
92.257.1003.0	cable assembly GST18I5KSB- 15 10TR01	gesis® CLASSIC connection cable, female - free end, number of poles 5, rated voltage 250 V / 400 V, rated current 16 A, cable type H05VV-F, fire class Eca, total length 1 m, nominal cross section conductor 1.5 mm², color of coding/ contact carrier tomato red