

product data sheet

item no. 83.040.1511.0

IP switch WIENET FS 16-PN-W

wieNET IP Switch, 16-Port Entry-Level Managed Fast Ethernet Switch with PROFINET support, Conformance Class B, 16 Ports 10/100 Mbps RJ45, IXM function enables fast deployment, GSDML-file, Management SNMP v1/v2/v3, Web-Browser, Standard MIB, Private MIB, Media Redundancy Protocol (MRP), Power Supply 8,4 V ... 52,8 V DC, Operating temperature -40 bis 75 ° C (-40°F ... 167°F)



item no.	83.040.1511.0
EAN	4049088435591
order unit	1 piece(s)

certificates / approvals



technical data

mounting method	DIN rail (top hat rail)
degree of protection (IP)	IP30
housing material	metal
manageable	yes
ethernet	yes
power over Ethernet	no
Fast Ethernet	yes
number of ports 10/100 Mbps RJ45	16
supported protocols	PROFINET
diagnostic LEDs	power/link status/data/data rate
10 gigabit Ethernet	no
number of ports 100 Mbps SC	0
type of electric connection	push-in connection//true
connector cross section	0.25mm²...2.5mm² (AWG26...AWG12)
wire strip length	8 mm

technical data

voltage type	DC
min. operating temperature	-40 °C
max. operation temperature	75 °C
storage temperature / transport min.	-40 °C
storage temperature / transport max.	85 °C
relative humidity min.	10 %
relative humidity max.	95 %
net weight	670 g
redundant power supply	2 power inputs

supply circuit

voltage type	DC
operating voltage min.	12 V
operating voltage max.	48 V
input current, max.	1.5 A


dimensions

depth	84 mm
width	74 mm
height	120 mm
weight	670 g

accessories

item no.	type	description
78.999.4000.0	patch-cables MOD ZBH RJ45 0,25 m	
78.999.4100.0	patch-cables MOD ZBH RJ45 0,5 m	
78.999.4200.0	patch-cables MOD ZBH RJ45 1,0 m	
78.999.4300.0	patch-cables MOD ZBH RJ45 2,0 m	
78.999.4400.0	patch-cables MOD ZBH RJ45 3,0 m	
78.999.4500.0	patch-cables MOD ZBH RJ45 5,0 m	
78.999.4600.0	patch-cables MOD ZBH RJ45 7,5 m	
78.999.4700.0	patch-cables MOD ZBH RJ45 10 m	

01-QU-RD-31/21



www.wieland-electric.com
eshop.wieland-electric.com

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten.
Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance			CAD-Zeichnung, keine manuellen Änderungen CAD-Drawing, no manual modifications allowed			1. Verwendung: First Use:			Blatt: Sheet:		
			Werkstoff/ Material		2018	Tag/ Date	Name		Zeichnung Nr. / Drawing No.		
		Maßstab/Scale			gezeichnet drawn	16.07.	Koetznner		83.040.1511.0 01K		
					Elektronische Freigabe Electronic Release						
								Maße in mm/Dimensions are in mm			
Datei/ File:			045771_A01K.DCD		Ersatz für/ Replacement for:						
		 wieland	Type		Benennung/ Title		Teilespezifikation / Component specification				
	08.07.21						IP-SWITCH / IP SWITCH				
Index	Datum/ Blatt Date/ Sheet						wienet FS 16-PN-W				
Änderung/ Revision											