product data sheet

item no. 83.040.1510.0

IP switch WIENET FS 8-PN-W

wieNET IP Switch, 8-Port Entry-Level Managed Fast Ethernet Switch with PROFINET support, Conformance Class B, 8 Ports 10/100 Mbps RJ45, IXM function enables fast deployment, GSDML-file, Management SNMP v1/v2/v3, Web-Browser, Standard MIB, Private MIB, Media Redundancy Protocol (MRP), Power Supply 8,4 V … 52,8 V DC, Operating temperature -40 bis 75 ° C (-40°F ... 167°F)



item no.	83.040.1510.0
EAN	4049088435584
order unit	1 piece(s)

certificates / approvals

technical data

mounting method	DIN rail (top hat rail)
degree of protection (IP)	IP30
housing material	metal
manageable	yes
ethernet	yes
power over Ethernet	no
Fast Ethernet	yes
Gigabit Ethernet	no
number of ports 10/100 Mbps RJ45	8
supported protocols	PROFINET
diagnostic LEDs	power/link status/data/data rate
10 gigabit Ethernet	no
number of ports 100 Mbps SC	0
type of electric connection	push-In connection//true
connector cross section	0.25mm²...2.5mm² (AWG26...AWG12)
wire strip length	8 mm

technical data

voltage type	DC
min. operating temperature	-40 °C
max. operation temperature	75 °C
storage temperature / transport min.	-40 °C
storage temperature / transport max.	85 °C
relative humidity min.	10 %
relative humidity max.	95 %
net weight	550 g
redundant power supply	2 power inputs

supply circuit

voltage type	DC
operating voltage min.	12 V
operating voltage max.	48 V
input current, max.	1.5 A


dimensions

depth	84 mm
width	43 mm
height	120 mm
weight	550 g

accessories

item no.	type	description
78.999.4000.0	patch-cables MOD ZBH RJ45 0,25 m	
78.999.4100.0	patch-cables MOD ZBH RJ45 0,5 m	
78.999.4200.0	patch-cables MOD ZBH RJ45 1,0 m	
78.999.4300.0	patch-cables MOD ZBH RJ45 2,0 m	
78.999.4400.0	patch-cables MOD ZBH RJ45 3,0 m	
78.999.4500.0	patch-cables MOD ZBH RJ45 5,0 m	
78.999.4600.0	patch-cables MOD ZBH RJ45 7,5 m	
78.999.4700.0	patch-cables MOD ZBH RJ45 10 m	

technical drawing



Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.

01-QU-RD-31/21

Teile-Nr. / Part No.	Typ / Type
83.040.1500.0	wienet FS-8-EI-W
83.040.1510.0	wienet FS-8-PN-W

Weitere Angaben siehe KATALOG oder eKatalog. Additional data see CATALOG or eCatalog.
www.wieland-electric.com
eshop.wieland-electric.com

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten.
Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance
CAD-Zeichnung, keine manuellen Änderungen CAD-Drawing, no manual modifications allowed
1. Verwendung: First Use:
Blatt: Sheet:

Werkstoff/ Material
Maßstab/Scale
2018 | Tag/ Date | Name
gezeichnet drawn | 22.01. | Koetzner
Elektronische Freigabe Electronic Release
Zeichnung Nr./ Drawing No.
T 83.040.1500.0 01K
Maße in mm/Dimensions are in mm
Datei/ File: 045711_A01K.DCD
Ersatz für/ Replacement for:

wieland

Type
Benennung/ Title
Teilespezifikation / Component specification
IP SWITCH

ⓐ 08.07.21
Index | Datum/ Blatt Date/ Sheet
Änderung/ Revision

83_040_1500_001K_1 CADW5014 Koetzner 2021-07-08T11:33:41 1.000