product data sheet

item no. 96.074.4053.9

connector RST20I7S S1 YR1 BL07

RST® CLASSIC connector, angled 90°, number of poles 7, male, connection type screw connection, rated voltage 250 V / 400 V, rated current 20 A, cable diameter 6 - 10 mm, color of coding/ contact carrier light blue



item no.	96.074.4053.9
EAN	4049088424335
order unit	100 piece(s)

certificates / approvals

technical data

note

note	wires with 2.5 mm² only without ferrules3 poles max. 20A, 4 poles max. 5A

general

rated current	20 A
rated voltage	250 V / 400 V
rated impulse voltage	4 kV
strain relief	yes
pollution degree	3
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	light blue
marking of poles	1, 2, 3, 4/N, 5, 6, 7
color of housing inclusive strain relief	black
RAL-Nummer Codierung/Kontakteinsatz	5012

connection data

cable diameter max.	10 mm
cable diameter min.	6 mm
connection cross section solid mm² max.	1.5 mm²
connection cross section solid mm² min.	0.2 mm²
connection cross section fine stranded mm² max.	2.5 mm²
connection cross section fine stranded mm² min.	0.2 mm²
terminations per pole	1
sheath strip length	25 mm
wire strip length	8 mm

model

model	male
connection type	screw connection
degree of protection (IP)	IP66/68 (3m;2h) /IP69

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	0.356 kWh/St
insulation components continous temperature	100 °C
surface finish	silver-plated

dimensions

length	71 mm
width	34.6 mm
height	63.8 mm


accessories


item no.	type	description
99.591.0000.7	cover for male connector SW	RST20i7/6 cover piece, for covering unused male connectors, with fastening belt, color black
Z5.569.5353.1	cover for male connector SW	RST20i7/6 cover piece, for covering unused male connectors, color black

assembly


item no.	type	description
96.071.4053.9	connector RST20I7S B1 ZR BL07	RST® CLASSIC connector, straight, number of poles 7, female, connection type screw connection, rated voltage 250 V / 400 V, rated current 16 A, cable diameter 6 - 10 mm, color of coding/ contact carrier light blue
9L.071.4053.9	connector RST20I7S 11 ZR1 BL07	RST® CLASSIC connector, straight, number of poles 7, female, connection type screw connection, rated voltage 250 V / 400 V, rated current 16 A, cable diameter 6 - 10 mm, longitudinal sealing yes, color of coding/ contact carrier light blue
96.071.6053.9	device connector RST20I7S B1 M00V BL07	RST® CLASSIC device connector, modular, straight, M20, number of poles 7, model female, connection type screw connection, rated voltage 250 V / 400 V, rated current 20 A, color of coding/ contact carrier light blue
9L.071.6053.9	device connector RST20I7S 11 M00V BL07	RST® CLASSIC device connector, modular, straight, M20, number of poles 7, model female, connection type screw connection, rated voltage 250 V / 400 V, rated current 20 A, longitudinal sealing yes, color of coding/ contact carrier light blue
96.071.6153.9	device connector RST20I7S B1 M03V BL07	RST® CLASSIC device connector, modular, straight, M16, number of poles 7, model female, connection type screw connection, rated voltage 250 V / 400 V, rated current 20 A, color of coding/ contact carrier light blue
9L.071.6153.9	device connector RST20I7S 11 M03V BL07	RST® CLASSIC device connector, modular, straight, M16, number of poles 7, model female, connection type screw connection, rated voltage 250 V / 400 V, rated current 20 A, longitudinal sealing yes, color of coding/ contact carrier light blue
96.073.6053.9	device connector RST20I7S B1 M90V BL07	RST® CLASSIC device connector, modular, angled 90°, M20, number of poles 7, model female, connection type screw connection, rated voltage 250 V / 400 V, rated current 20 A, color of coding/ contact carrier light blue
96.075.6153.9	device connector RST20I7S B1 M13V BL07	RST® CLASSIC device connector, modular, angled 7°, M16, number of poles 7, model female, connection type screw connection, rated voltage 250 V / 400 V, rated current 20 A, color of coding/ contact carrier light blue
96.073.6253.9	device connector RST20I7S B1 M90V BL07	RST® CLASSIC device connector, modular, angled 90°, M25, number of poles 7, model female, connection type screw connection, rated voltage 250 V / 400 V, rated current 20 A, color of coding/ contact carrier light blue
96.071.6253.9	device connector RST20I7S B1 M01V BL07	RST® CLASSIC device connector, modular, straight, M25, number of poles 7, model female, connection type screw connection, rated voltage 250 V / 400 V, rated current 20 A, color of coding/ contact carrier light blue
9L.071.6253.9	device connector RST20I7S B1 M01V BL07	RST® CLASSIC device connector, modular, straight, M25, number of poles 7, model female, connection type screw connection, rated voltage 250 V / 400 V, rated current 20 A, longitudinal sealing yes, color of coding/ contact carrier light blue


technical drawing










Auslieferungszustand
/delivery status





Teile-Nr./ Part no.	Typ/ Type	Kodierung/ coding
96.074.4053.0	RST2017S S1 YR1 GL	
96.074.4053.1	RST2017S S1 YR1 SW	
96.074.4053.9	RST2017S S1 YR1 BL07	
96.064.4053.6	RST2016S S1 YR1 TB04	
96.074.4053.6	RST2017S S1 YR1 TB04	

1:2



● = Pol verschlossen /pole closed

These dimensions will be especially checked at delivery
Only inspection dimensions
With /E marked dimensions are only valid for internal use

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.

Tolerierung Size ISO 14405 Ⓔ / Tolerance system Size ISO 14405 Ⓔ.
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten. Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1. Verwendung: First Use:

Blatt: 1 von 1
Sheet: 1 of 1

Werkstoff / Material

Maßstab / Scale: 1:1

Vol. mm³ Oft./Srf. mm²

	Tag/Date	Name
gezeichnet drawn	16.11.2017	Hollet
geprüft checked		
Normgeor. Stand. check		

Zeichnung Nr. / Drawing No.: 96.074.4053.0 13K

Index: a

Maße in mm / Dimensions are in mm

Ersatz für / Replacement for:

Index	Datum / Blatt Date / Sheet	Änderung / Revision
a	14.05.2018 /	

wieland
www.wieland-electric.com

Type: RST20I

Bennenung/Title:

ST_SCHRAUBE

ohne Drahtschutz

male, screw connection without wire protection