product data sheet

item no. 00.712.1323.1

flat cable 5G2,5+2x1,5 PVC OS

gesis® NRG BASIC+SIGNAL flat cable; mains 5G2.5; 20 A; 0.6/1 kV; bus 2X1.5; 6 A; 250 V; unshielded; PVC CPR class Eca; color: black.



item no.	00.712.1323.1
EAN	4049088354120
order unit	1 piece(s)

certificates / approvals

technical data

general

rated voltage	600 V / 1.000 V
rated current	20 A
mechanical coding	yes

technical data

nominal cross section conductor	2.5 mm²
nominal voltage UN	1000 V
nominal voltage U0	600 V
bending radius, static	100 mm
fire class	Eca
conductor category	class 5 = flexible
number of cores	7
core insulation	PE
yellow/green conductor	yes
screen	no
material outer sheath	PVC
color outer sheath	black
flame retardant	according to DIN 60332-1-2
halogen free (according to EN 60754-12)	no
cable width approx.	36.9 mm
cable height approx.	6.3 mm
ambient temperature min.	-15 °C
ambient temperature max.	70 °C
nominal voltage U0	600 V
nominal voltage U	1000 V

nominal cross section	1.5 mm²

model

nominal cross section conductor	2.5 mm²

material

halogen free	no
fire load	1.755 kWh/m

accessories

item no.	type	description
F0.000.0051.9	cutting tool podis/gesis	Cutter for podis and gesis cables up to 5G16 (AWG 5C6), blade length 40 mm
05.562.3000.0	cable clip Befestigungsschelle	Cable clip for flat cable

assembly

item no.	type	description
91.922.2453.0	connector GST15I2S S1 ZF1 W PB01	gesis® MINI connector, number of poles 2, male, connection type screw connection, rated voltage 250 V, rated current 6 A, cable diameter 3.4 - 5.5 mm, color of coding/ contact carrier pastel blue
92.050.1553.1	flat cable adapter GST18I5A S1 F7 SW	gesis® NRG mains feed-in for flat cable; colour: black; 250/400 V; 20 A; IP40; integrated strain-relief to feed-in with round cables, diameter: 12 to 16 mm, cross-section fine-stranded: 2,5 bis 4 mm², solid: 2,5-6 mm²; Piercing-contact screws with Torx-head; for gesis® NRG flat cable 5G2,5, 5G4, 5G2,5+2x1,5 and 5G4+2x1,5
92.031.5453.1	flat cable adapter GST18I3I B1H F7V SW	gesis® NRG flat cable adapter to GST18i3; Code 1 mains; colour of coding: black; pre-selection of L1 or L2 or L3; 250 V; 20 A; IP20; pluggable output parallel to flat cable; piercing-contact screws with Torx-head; for gesis® NRG flat cable 5G2,5, 5G4, 5G2,5+2x1,5 and 5G4+2x1,5
92.051.5453.1	flat cable adapter GST18I5I B1H F7V SW	gesis® NRG flat cable adapter to GST18i5; Code 1 mains; colour of coding: black; 250/400 V; 20 A; pluggable output parallel to flat cable; piercing-contact screws with Torx-head; for gesis® NRG flatcable 5G2,5, 5G4, 5G2,5+2x1,5 und 5G4+2x1,5
91.020.5453.0	flat cable adapter GST15I2A SI	gesis® NRG bus feed-in for flat cable; colour: black; 250 V; 6 A; IP20; integrated strain-relief to feed-in with round cables; diameter: 5,9 to 7,5 mm; cross-section 0,5 to 1,5 mm²; piercing-contact screws with Torx-head; for gesis® NRG flat cable 5G2,5+2x1,5 and 5G4+2x1,5 with unshielded bus.
91.021.5453.0	flat cable adapter GST15I2I B1H PB02	gesis® NRG flat cable adapter GST15i2; color of coding: pastel blue; 250 V; 6 A; IP20; tap off of the signal of the combined flat cable BASIC+SIGNAL with unshielded bus; pluggable output parallel to flat cable; piercing-contact screws with Torx-head; for gesis® NRG flat cable 5G2,5+2x1,5 and 5G4+2x1,5 with unshielded bus.
92.051.5653.0	flat cable adapter GST18I5I B1H F7V PB02	gesis® NRG flat cable adapter to GST18i5; Code 2 mains + not SELV; colour of coding: pastel blue; pre-selection of L1 or L2 or L3; 250 V; 20 A; pluggable output parallel to flat cable; piercing-contact screws with Torx-head; for gesis® NRG flatcable without shield 5G2,5+2x1,5 und 5G4+2x1,5.
06.562.9753.0	end cap GESIS NRG 5+2	gesis® NRG end cap; for flat cable 5G2,5/4+2X1,5 Basic + Signal; IP40; rated voltage 250 V; can be assembled after cable is cut with cutting tool; colour: natural coloured