product data sheet

item no. 9L.073.4153.9

# connector RST20I7S 11 YR2 BL07

RST20i7 Connector, angled 90°, number of poles 7, female, connection type screw connection, rated voltage 250 V / 400 V, rated current 20 A, cable diameter 10 - 10 mm, longitudinal sealing yes, color of coding/ contact carrier light blue



| | |
|---|---|
| item no. | 9L.073.4153.9 |
| EAN | 4049088425646 |
| order unit | 100 piece(s) |

## certificates / approvals

## technical data

**note**

| | |
|---|---|
| note | wires with 2.5 mm² only without ferrules3 poles max. 20A, 4 poles max. 5AUse only one connector with contact sealing - either male or female connector. |

**general**

| | |
|---|---|
| rated current | 20 A |
| rated voltage | 250 V / 400 V |
| rated impulse voltage | 4 kV |
| strain relief | yes |
| pollution degree | 3 |
| lockable | self-locking (unlocking by tool) |
| color of coding/ contact carrier | light blue |
| marking of poles | 1, 2, 3, 4/N, 5, 6, 7 |
| color of housing inclusive strain relief | black |

**connection data**

| | |
|---|---|
| cable diameter max. | 10 mm |
| cable diameter min. | 10 mm |
| connection cross section solid mm² max. | 1.5 mm² |
| connection cross section solid mm² min. | 0.2 mm² |
| connection cross section fine stranded mm² max. | 2.5 mm² |
| connection cross section fine stranded mm² min. | 0.2 mm² |
| terminations per pole | 1 |
| sheath strip length | 25 mm |
| wire strip length | 8 mm |

**model**

| | |
|---|---|
| model | female |
| connection type | screw connection |
| degree of protection (IP) | IP66/68 (3m;2h) /IP69 |

| | |
|---|---|
| longitudinal sealing | yes |

**material**

| | |
|---|---|
| housing material | polyamide |
| halogen free | yes |
| contact material | CuZn |
| fire load | 0.356 kWh |
| insulation components continous temperature | 100 °C |
| surface finish | silver-plated |

**dimensions**

| | |
|---|---|
| length | 75.3 mm |
| width | 34.6 mm |
| height | 63.8 mm |

## accessories

| item no. | type | description |
|---|---|---|
| 06.562.8753.0 | manual disconnect RST20i7 BG | Manual disconnect for later installation of RST20i7/i6 connectors, color concrete gray |
| 99.589.0000.7 | cover for female connector SW | RST20i7/6 cover piece, for covering unused female connectors, with fastening belt, color black |
| Z5.569.5253.1 | cover for female connector SW | RST20i7/6 cover piece, for covering unused female connectors, color black |

## assembly


| item no. | type | description |
|---|---|---|
| 96.072.4153.9 | connector RST20I7S S1 ZR2 BL07 | RST20i7 Connector, straight, number of poles 7, male, connection type screw connection, rated voltage 250 V / 400 V, rated current 16 A, cable diameter 10 - 14 mm, color of coding/ contact carrier light blue |
| 96.072.6053.9 | device connector RST20I7S S1 M00V BL07 | RST20i7 Device connector, modular, straight, M20, number of poles 7, model male, connection type screw connection, rated voltage 250 V / 400 V, rated current 20 A, color of coding/ contact carrier light blue |
| 96.072.6153.9 | device connector RST20I7S S1 M03V BL07 | RST20i7 Device connector, modular, straight, M16, number of poles 7, model male, connection type screw connection, rated voltage 250 V / 400 V, rated current 20 A, color of coding/ contact carrier light blue |
| 96.074.6053.9 | device connector RST20I7S S1 M90V BL07 | RST20i7 Device connector, modular, angled 90°, M20, number of poles 7, model male, connection type screw connection, rated voltage 250 V / 400 V, rated current 20 A, color of coding/ contact carrier light blue |
| 96.076.6153.9 | device connector RST20I7S S1 M13V BL07 | RST20i7 Device connector, modular, angled 7°, M16, number of poles 7, model male, connection type screw connection, rated voltage 250 V / 400 V, rated current 20 A, color of coding/ contact carrier light blue |
| 96.074.6253.9 | device connector RST20I7S S1 M91V BL07 | RST20i7 Device connector, modular, angled 90°, M25, number of poles 7, model male, connection type screw connection, rated voltage 250 V / 400 V, rated current 20 A, color of coding/ contact carrier light blue |
| 96.072.6253.9 | device connector RST20I7S B1 M01V BL07 | RST20i7 Device connector, modular, straight, M25, number of poles 7, model male, connection type screw connection, rated voltage 250 V / 400 V, rated current 20 A, color of coding/ contact carrier light blue |


technical drawing

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.


These dimensions will be especially checked at delivery
Only inspection dimensions
With /E marked dimensions are only valid for internal use


Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig









Auslieferungszustand
/delivery status





| Teile-Nr./ Part no. | Typ/ Type | | Kodierung/ coding |
|---|---|---|---|
| 96.073.4153.0 | RST20I7S B1 YR2 | GL |  |
| 96.073.4153.1 | RST20I7S B1 YR2 | SW | |
| 9L.073.4153.0 | RST20I7S 11 YR2 | GL | |
| 9L.073.4153.1 | RST20I7S 11 YR2 | SW | |
| 96.073.4153.9 | RST20I7S B1 YR2 | BL07 |  |
| 9L.073.4153.9 | RST20I7S 11 YR2 | BL07 | |
| 96.063.4153.6 | RST20I6S B1 YR2 | TB04 |  |
| 9L.063.4153.6 | RST20I6S 11 YR2 | TB04 | |
| 96.073.4153.6 | RST20I7S B1 YR2 | TB04 |  |
| 9L.073.4153.6 | RST20I7S 11 YR2 | TB04 | |

1:2



● = Pol verschlossen /pole closed

Tolerierung Size ISO 14405 Ⓔ / Tolerance system Size ISO 14405 Ⓔ.
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten. Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1. Verwendung: First Use:

Blatt: 1 von 1
Sheet: 1 of 1

Werkstoff / Material

Maßstab / Scale: 1:1

Vol. mm³ Oft./Srf. mm²

Ersatz für / Replacement for:

| | Tag/Date | Name |
|---|---|---|
| gezeichnet drawn | 16.11.2017 | Hollet |
| geprüft checked | | |
| Normgeor. Stand. check | | |

Zeichnung Nr. / Drawing No.: 96.073.4153.0 13K

Index: a

Maße in mm / Dimensions are in mm

| Index | Datum / Blatt Date / Sheet | Änderung / Revision |
|---|---|---|
| / | | |
| / | | |
| / | | |
| / | | |
| / | | |
| / | | |
| a | 14.05.2018 / | |

wieland
www.wieland-electric.com

Type: RST20I

Bennenung/Title: BU_SCHRAUB
ohne Drahtschutz
female, screw connection without wire protection