product data sheet

item no. 46.032.5056.7

device connector RST16I3/2S S1 M02 GN

RST® MINI device connector, standard, straight, M16, number of poles 2, model male, connection type screw connection, rated voltage 250 V / 400 V, rated current 16 A, color of coding/ contact carrier leaves green



item no.	46.032.5056.7
EAN	4049088546044
order unit	100 piece(s)

certificates / approvals

technical data

note

note	RST® terminals with screw clamping allow the connection of conductors without special preparation (without ferrules) according to EN 60999-1.positioning realised with flattened thread

general

rated current	16 A
rated voltage	250 V / 400 V
pollution degree	3
rated impulse voltage	4 kV
continuity resistor	0.75 mOhm
lockable	self-locking (unlocking by hand)
color of coding/ contact carrier	leaves green
Pole codification	1, 2

connection data

connection cross section solid mm² max.	2.5 mm²
connection cross section solid mm² min.	0.25 mm²
connection cross section fine stranded mm² max.	2.5 mm²
connection cross section fine stranded mm² min.	0.25 mm²
terminations per pole	1
wire strip length	8 mm

model

model	male
connection type	screw connection
connecting thread metric	M16

material

housing material	polyamide
halogen free	yes

contact material	CuZn
fire load	0.043 kWh/St
insulation components continous temperature	100 °C
surface finish	silver-plated

dimensions

length	35.2 mm
width	19.9 mm
height	19.9 mm

accessories

item no.	type	description
06.563.8853.1	cover for male connector SW	RST16i3/2 cover piece, for covering unused male connectors, color black
06.563.8953.1	cover for male connector SW	RST16i3/2 cover piece, for covering unused male connectors, with fastening belt, color black

assembly

item no.	type	description
46.031.4556.7	connector BUCHSENTEIL+ZE RST16I3/2S B1 ZT4 S GN	RST® MINI connector, straight, number of poles 2, female, connection type screw connection, rated voltage 250 V / 400 V, rated current 16 A, cable diameter 5 - 10.6 mm, color of coding/ contact carrier leaves green


technical drawing


Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.

These dimensions will be especially checked at delivery
Only inspection dimensions
With /E marked dimensions are only valid for internal use


Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig


Kodierung
/coding






Auslieferungszustand
delivery status







Gehäuseausschnitt/
section of housing

Bestellnummer /order number	Typ /type	Kodierung /coding	Farbe /color
46.032.5051.6	RST16i3/2S S1 M02 A TB	C5	**türkisblau** /turquoiseblue
46.032.5054.9	RST16i3/2S S1 M02 H BL	C4	**lichtblau** /lightblue
46.032.5051.4	RST16i3/2S S1 M02 L BR	C3	**signalbraun** /signalbrown
46.032.5056.7	RST16i3/2S S1 M02 GN	C2	**laubgrün** /leaf green
46.032.5054.1	RST16i3/2S S1 M02 SW	C1	**schwarz** /black
46.032.5054.0	RST16i3/2S S1 M02 GL	C1	**lichtgrau** /lightgrey

Weitere Daten siehe KATALOG oder eKatalog.
Additional data see CATALOG or eCatalog.

www.wieland-electric.com
eshop.wieland-electric.com

Tolerierung Size ISO 14405 Ⓔ / Tolerance system Size ISO 14405 Ⓔ.
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten.
Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1. Verwendung: First Use:

Blatt: 1 von 1
Sheet: 1 of 1

Werkstoff / Material

Maßstab / Scale: 1:1

	Tag/Date	Name
gezeichnet drawn	12.07.2016	Hollet
geprüft checked		
Norm gepr. Stand. check		

Zeichnung Nr. / Drawing No.: 46.032.5054.0 13K

Index: c

Maße in mm / Dimensions are in mm

Vol. mm³ Ofl./Srf. mm²

Ersatz für / Replacement for:

Index	Datum / Blatt Date / Sheet	Änderung / Revision
c	01.09.2026 /	
b	09.05.2019 /	

wieland
www.wieland-electric.com

Type: RST16I2

Bennenung/Title

STECKERTEIL

Geräteanschluss, 2polig^M
male connector, device connection, 2pole

2026-10-21 11:02:09 1.000

QU-MEE-01/14 a