product data sheet

item no. 4L.022.3041.4

## connector RST08i3/2S 21 ZR1SHL SG

RST® MICRO connector, straight, number of poles 2, male, connection type screw connection, rated voltage 50 V / 120 V, rated current 8 A, cable diameter 4 - 7 mm, longitudinal sealing yes, color of coding/ contact carrier slate grey



| | |
|---|---|
| item no. | 4L.022.3041.4 |
| EAN | 4049088482236 |
| order unit | 50 piece(s) |

### certificates / approvals

### technical data

**note**

| | |
|---|---|
| note | RST® terminals with screw clamping allow the connection of conductors without special preparation (without ferrules) according to EN 60999-1.Use only one connector with contact sealing - either male or female connector. |

**general**

| | |
|---|---|
| rated current | 8 A |
| rated voltage | 50 V / 120 V |
| rated impulse voltage | 2.5 kV |
| strain relief | yes |
| pollution degree | 3 |
| lockable | self-locking (unlocking by hand) |
| color of coding/ contact carrier | slate grey |
| marking of poles | 1, 2 |
| color of housing inclusive strain relief | black |
| RAL-Nummer Codierung/Kontakteinsatz | 7015 |

**connection data**

| | |
|---|---|
| cable diameter max. | 7 mm |
| cable diameter min. | 4 mm |
| connection cross section solid mm² max. | 1 mm² |
| connection cross section solid mm² min. | 0.2 mm² |
| connection cross section fine stranded mm² max. | 1 mm² |
| connection cross section fine stranded mm² min. | 0.22 mm² |
| terminations per pole | 1 |
| sheath strip length | 18 mm |
| wire strip length | 6 mm |

**model**

| | |
|---|---|
| model | male |

| | |
|---|---|
| connection type | screw connection |
| degree of protection (IP) | IP66/68 (3m;2h) /IP69 |
| longitudinal sealing | yes |

**material**

| | |
|---|---|
| housing material | polyamide |
| halogen free | yes |
| contact material | CuZn |
| fire load | 0.014 kWh/St |
| insulation components continous temperature | 100 °C |
| surface finish | silver-plated |

**dimensions**

| | |
|---|---|
| length | 41.8 mm |
| width | 14.9 mm |
| height | 14.9 mm |

## accessories


| item no. | type | description |
|---|---|---|
| 06.563.5153.1 | cover for male connector SW | RST08i3/2 cover piece, for covering unused male connectors, with fastening belt, color black |
| 06.502.6100.0 | allen key RST MICRO SW 0,9 | Allen Key for screw terminals RST® MICRO |
| 06.502.6300.0 | screwdriver RST MICRO SW 0,9 | Screwdriver (hexagonal wrench 0.9) for RST® MICRO |

## assembly

| item no. | type | description |
|---|---|---|
| 41.021.4041.4 | device connector RST08i3/2S B1 M02HL SG | RST® MICRO device connector, standard, straight, M14, number of poles 2, model female, connection type screw connection, rated voltage 50 V / 120 V, rated current 8 A, color of coding/ contact carrier slate grey |

technical drawing

Gezeichnete Ausführung/drawn version
41.032.3053.1





Auslieferungszustand/
*delivery status*



| Teile-Nr. *I part-no.* | Type | Kodierung *I coding* |
|---|---|---|
| 41.032.3053.1 | RST08i3 S S1 ZR1 H SW | C1 |
| 4L.032.3053.1 | RST08i3 S 21 ZR1 H SW | |
| 41.032.3043.9 | RST08i3 S S1 ZR1SH BL | C2 |
| 4L.032.3043.9 | RST08i3 S 21 ZR1SH BL | |
| 41.032.3041.4 | RST08i3 S S1 ZR1SHL SG | C3 |
| 4L.032.3041.4 | RST08i3 S 21 ZR1SHL SG | |
| 41.032.3051.8 | RST08i3 S S1 ZR1SHL KG | C4 |
| 4L.032.3051.8 | RST08i3 S 21 ZR1SHL KG | |
| 41.022.3043.1 | RST08i3/2S S1 ZR1 H SW | C1 |
| 4L.022.3043.1 | RST08i3/2S 21 ZR1 H SW | |
| 41.022.3043.9 | RST08i3/2S S1 ZR1SH BL | C2 |
| 4L.022.3043.9 | RST08i3/2S 21 ZR1SH BL | |
| 41.022.3041.4 | RST08i3/2S S1 ZR1SHL SG | C3 |
| 4L.022.3041.4 | RST08i3/2S 21 ZR1SHL SG | |
| 41.022.3041.8 | RST08i3/2S S1 ZR1SHL KG | C4 |
| 4L.022.3041.8 | RST08i3/2S 21 ZR1SHL KG | |

1:1



● =Pol nicht bestückt
*I pole not mounted*

Weitere Daten siehe KATALOG oder eKatalog
additional data see CATALOG or eCATALOG

www.wieland-electric.com
eshop.wieland-electric.com

Tolerierung Size ISO 14405 Ⓔ / Tolerance system Size ISO 14405 Ⓔ.
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten. / conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach
General tolerance

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1. Verwendung:
First Use:

Blatt: 1 von 1
Sheet: 1 of 1

Werkstoff / Material

Maßstab / Scale: 1:1

Vol. mm³ Ofl./Srf. mm²

| | Tag/Date | Name |
|---|---|---|
| gezeichnet / drawn | 22.02.2018 | Hollet |
| geprüft / checked | | |
| Norm gepr. Stand. check | | |

Zeichnung Nr. / Drawing No.: 41.032.3053.1 13K

Index: a

Maße in mm / Dimensions are in mm

Ersatz für / Replacement for:

| Index | Datum / Blatt Date / Sheet | Änderung / Revision |
|---|---|---|
| a | 12.03.2020 / | |

wieland
www.wieland-electric.com

Type: RSTmicro

Bennenung/Title: STECKERTEIL_FA_ZE
male with strain relief

41_032_3053_1_13K_sheet_1 CADW4030 Hollet 2020-03-12T14:20:51 1.000

QU-MEE-01/14 a

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit Ⓔ gekennzeichnete Maße sind nur für interne Zwecke gültig

These dimensions will be especially checked at delivery
Only inspection dimensions
With Ⓔ marked dimensions are only valid for internal use

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.