product data sheet

item no. 96.022.0451.4

connector RST20I2F S23ZRWSVL BR01

RST20i2 Connector, straight, number of poles 2, male, connection type spring clamp connection, rated voltage 50 V / 120 V, rated current 20 A, Illumination cable (13.3x5.3), color of coding/ contact carrier signal brown



item no.	96.022.0451.4
EAN	4049088436444
order unit	100 piece(s)

certificates / approvals

c UL us LISTED

technical data

note

note	fine stranded and stranded conductors require cable end sleeve

general

rated current	20 A
rated voltage	50 V / 120 V
rated impulse voltage	4 kV
strain relief	yes
pollution degree	3
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	signal brown
marking of poles	1, 2
color of housing inclusive strain relief	black

connection data

cable diameter max.	13.3 mm
cable diameter min.	5.3 mm
connection cross section solid mm² max.	2.5 mm²
connection cross section solid mm² min.	0.5 mm²
connection cross section fine stranded mm² max.	1.5 mm²
connection cross section fine stranded mm² min.	0.5 mm²
terminations per pole	2
special cable geometry	illumination cable (13.3x5.3)
connection cross section stranded mm² min.	0.75 mm²
connection cross section stranded mm² max.	1.5 mm²
sheath strip length	35 mm

model

model	male
connection type	spring clamp connection

degree of protection (IP)	IP66/68 (3m;2h) /IP69

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	0.272 kWh
insulation components continous temperature	100 °C
surface finish	silver-plated

dimensions

length	79.1 mm
width	34.6 mm
height	34.6 mm

accessories

item no.	type	description
05.564.4453.1	cover for male connector SW	RST20i3/2 cover piece, for covering unused male connectors, color black
99.416.6205.2	cover for male connector SW	RST20i3/2 cover piece, for covering unused male connectors, with fastening belt, color black
06.502.4300.0	screwdriver DIN 5264 A 0,4 X 2,5	Screw driver according to DIN 5264 A, blade: 0.4x2.5 mm, long and straight version
95.101.1300.0	ferrule crimping tool 0,08 - 10 mm²	Crimping tool for ferrules, wire strip length: 7-28 mm, nominal cross section: 0,08-10 mm², length of tool: 180 mm
06.600.3627.0	ferrule DIN 46228-E1-12	RST ferrule, for spring clamp contact, with insulating sleeve, for cross section 1.0 mm²/AWG17
06.600.3727.0	ferrule DIN 46228-E0,75-12	RST ferrule, for spring clamp contact, with insulating sleeve, for cross section 0.75-1.0 mm²/AWG17
06.600.3827.0	ferrule DIN 46228-E0,5-10	RST ferrule, for spring clamp contact, with insulating sleeve, for cross section 0.5 mm²/AWG20
06.600.3927.0	ferrule DIN 46228-E1,5-12	RST ferrule, for spring clamp contact, with insulating sleeve, for cross section 1.5 mm²/AWG16

assembly


item no.	type	description
96.020.0151.4	distributor RST20I2V 3P1 F V L BR0	RST20i2 Distributor, parallel connection, with fastening option, number of poles 2, rated voltage 50 V / 120 V, rated current 20 A, number of inputs 1, number of outputs 3, color of coding/ contact carrier signal brown
96.021.0451.4	connector RST20I2F B23ZRWS L BR01	RST20i2 Connector, straight, number of poles 2, female, connection type spring clamp connection, rated voltage 50 V / 120 V, rated current 20 A, Illumination cable (13.3x5.3), color of coding/ contact carrier signal brown


technical drawing

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.


Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig

These dimensions will be especially checked at delivery
Only inspection dimensions
With /E marked dimensions are only valid for internal use






Auslieferungszustand
delivery status



Verpackungseinheit: 100 Stück
packaging unit: 100



96.022.0451.4	RST2012F S23ZRWSVL BR01	signalbraun/signal brown
Bestellnummer /order number	Typ /type	Farbe /colour

Weitere Daten siehe KATALOG oder eKATALOG.
Additional data see CATALOG or eCATALOG.

www.wieland-electric.com
eshop.wieland-electric.com

Tolerierung Size ISO 14405 Ⓔ / Tolerance system Size ISO 14405 Ⓔ.
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten.
Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1. Verwendung: First Use:

Blatt: 1 von 1
Sheet: 1 of 1

Werkstoff / Material

Maßstab / Scale: 1:1

Vol. mm³ Ofl./Srf. mm²

	Tag/Date	Name
gezeichnet drawn	19.05.2017	Duetsch T .
geprüft checked		
Normgeor. Stand. check		

Zeichnung Nr. / Drawing No.: 96.022.0451.4 13K

Index

Maße in mm / Dimensions are in mm

Ersatz für / Replacement for:

Index | Datum / Blatt Date / Sheet | Änderung / Revision

wieland
www.wieland-electric.com

Type: RST2012F S23ZRWS VL BR01

Bennenung/Title: STECKERTEIL + ZE
Federkraftanschluss / spring clamp connection
50V 20A