UL Product iQ™

NMTR.E169904 - POWER CIRCUIT AND MOTOR-MOUNTED APPARATUS

Power Circuit and Motor-mounted Apparatus

See General Information for Power Circuit and Motor-mounted Apparatus

WIELAND ELECTRIC GMBH E169904
BRENNERSTRASSE 10-14
96052 BAMBERG, GERMANY

Low voltage modules Model(s) ADW*, AKB*, AKT*, ASV

CORES PT, followed by -2, -3 or -4, followed by -+50, 100, 150, 200, 300, 400 or 500, may be followed by S, followed by 0-10V, 0-20MA or 4-20MA.

CSR*, DAW*, DSQ-10V/20mA*, KSQ-10V*, UET*, UET-P*, UET-P/LCD*, UET/LCD*

Low voltage modules, open type "TM" Model(s) 99.800, 99.801, 99.804

Miscellaneous apparatus, electronic modules, open type Model(s) DIPOS E or DIPOS C, followed by 2 or 3, followed by PT, TC, KSQ or AKT, followed by 0, 1, 2, 3 or 4, followed by 00, 01, 02, 03, 04, 05, 06, 07, 08, 09, 10, 12, 20, 21, 31, 32, 33, 40 or 41, followed by 00, 01, 02, 03, 04, 05, 06, 07 or 08, may be followed by suffix S or F, may be followed by SW, LG or any other two digits.

Miscellaneous apparatus, open type "Wieland Relay System" Model(s) WRS-REL-1S-250V5A, WRS-REL-1W-250V16A, WRS-REL-1W-250V5A, WRS-REL-1W-48V20M, WRS-REL-2W-250V5A, WRS-REL-2W-48V20M, WRS-SS-AC1-250V4A, WRS-SS-AC1-250V6A, WRS-SS-DC-60V3A, WRS-SS-DC-60V5A, WRS-T115/230-300M, WRS-TIMER-250V5A

Miscellaneous apparatus, open type Model(s) PCM

Open-type Switch Mode Power Supplies Model(s) WIPOS PS1 24-20, WIPOS PS1 24-5

Power supplies Model(s) WIPOS P1 12-0.42, WIPOS P1 12-0.42-B, WIPOS P1 12-0.84, WIPOS P1 12-0.84-B, WIPOS P1 12-1.5, WIPOS P1 12-1.5-B, WIPOS P1 12-10, WIPOS P1 12-10-A, WIPOS P1 12-2.2-UPS, WIPOS P1 12-2.5, WIPOS P1 12-2.5-B, WIPOS P1 12-4.4-UPS, WIPOS P1 12-5, WIPOS P1 12-5-B, WIPOS P1 12-8.4, WIPOS P1 12-8.8-UPS, WIPOS P1 15-0.34, WIPOS P1 15-0.34-B, WIPOS P1 15-0.67, WIPOS P1 15-0.67-B, WIPOS P1 15-1.2, WIPOS P1 15-1.2-B, WIPOS P1 24-0.21, WIPOS P1 24-0.21-B, WIPOS P1 24-0.42, WIPOS P1 24-0.42-B, WIPOS P1 24-0.75, WIPOS P1 24-0.75-B, WIPOS P1 24-1.1-UPS, WIPOS P1 24-1.25, WIPOS P1 24-1.25-B, WIPOS P1 24-10, WIPOS P1 24-10-A, WIPOS P1 24-12.5, WIPOS P1 24-12.5-A, WIPOS P1 24-17.6-UPS, WIPOS P1 24-2.2-UPS, WIPOS P1 24-2.5, WIPOS P1 24-2.5-B, WIPOS P1 24-20, WIPOS P1 24-20-A, WIPOS P1 24-3.8, WIPOS P1 24-3.8-A, WIPOS P1 24-3.8-L, WIPOS P1 24-4.2, WIPOS P1 24-4.4-UPS, WIPOS P1 24-5, WIPOS P1 24-5-A, WIPOS P1 24-8.8-UPS, WIPOS P1 48-0.55-UPS, WIPOS P1 48-0.625, WIPOS P1 48-0.625-B, WIPOS P1 48-1.1-UPS, WIPOS P1 48-1.25, WIPOS P1 48-1.25-B, WIPOS P1 48-10, WIPOS P1 48-10-A, WIPOS P1 48-2.1, WIPOS P1 48-2.2-UPS, WIPOS P1 48-2.5, WIPOS P1 48-2.5-A, WIPOS P1 48-4.4-UPS, WIPOS P1 48-5, WIPOS P1 48-5-A, WIPOS P1 48-6.25, WIPOS P1 48-6.25-A, WIPOS P1 48-8.8-UPS, WIPOS P1 5-1, WIPOS P1 5-1-B, WIPOS P1 5-10, WIPOS P1 5-10-B, WIPOS P1 5-2, WIPOS P1 5-2-B, WIPOS P1 5-3, WIPOS P1 5-3-B, WIPOS P1 5-6, WIPOS P1 5-6-B, WIPOS P2 12-8.4, WIPOS P2 24-4.2, WIPOS P2 48-2.1, WIPOS P3 12-10, WIPOS P3 24-10, WIPOS P3 24-20, WIPOS P3 24-40, WIPOS P3 24-40-L, WIPOS P3 24-5, WIPOS P3 48-10, WIPOS P3 48-20, WIPOS P3 48-5, WIPOS PB1 12-0.83, WIPOS PB1 12-2, WIPOS PB1 12-2.75, WIPOS PB1 12-4.5, WIPOS PB1 12-6, WIPOS PB1 15-0.67, WIPOS PB1 15-1.6, WIPOS PB1 15-2.4, WIPOS PB1 15-4, WIPOS PB1 15-5, WIPOS PB1 24-0.42, WIPOS PB1 24-1, WIPOS PB1 24-1.5, WIPOS PB1 24-2.5, WIPOS PB1 24-3.8, WIPOS PB1 24-4.2, WIPOS PB1 5-1.5, WIPOS PB1 5-12, WIPOS PB1 5-3, WIPOS PB1 5-4.5, WIPOS PB1 5-7, WIPOS R20

Power supplies, open type Model(s) WIPOS 24VDC/1,25A 1 PH V, WIPOS 24VDC/10A 1 PH H, WIPOS 24VDC/10A 1 PH V, WIPOS 24VDC/2, 5A 1 PH H, WIPOS 24VDC/20A 1 PH H, WIPOS 24VDC/20A 3PH H, WIPOS 24VDC/2A 1 PH V, WIPOS 24VDC/40A 3 PH H, WIPOS 24VDC/5, 0A 1 PH H, WIPOS 24VDC/5, 0A 1PH V

Switching power supplies Model(s) WIPOS PS1 1.25, WIPOS PS1 2.5, WIPOS PS1 24-10

Terminal interfaces "TM31" Model(s) 6SL3760-0CB00-0AA0

Terminal interfaces Model(s) 99.802.5333.8, 99.805.5333.8, Buchse D-SUB 15, Buchse D-SUB 25, Buchse D-SUB 37, Buchse D-SUB 50, Buchse D-SUB 9, FLK-SR 10, FLK-SR 14, FLK-SR 16, FLK-SR 20, FLK-SR 26, FLK-SR 34, FLK-SR 40, FLK-SR 50, FLK-SR 60, FLK-SR 64, Stecker D-SUB 15, Stecker D-SUB 25, Stecker D-SUB 37, Stecker D-SUB 50, Stecker D-SUB 9

Investigated to ANSI/UL 508

Open Type, DC/DC Converter Model(s) wipos UPS 20-960

Power Circuit and Motor-Mounted Apparatus, Open Type Switching Power Supplies Model(s) wipos PSW 24-20, wipos PSW 48-10

* - May be followed by additional suffix letters and/or numbers.

Last Updated on 2018-09-13

Der Umstand, dass der Name oder das Produkt eines Unternehmens in dieser Datenbank aufgeführt ist, garantiert nicht, dass die Herstellung der jeweiligen Produkte dem Follow-Up-Service von UL unterliegt. Nur Produkte mit UL-Zeichen gelten als zertifiziert und sind vom Follow-Up-Service von UL abgedeckt. Prüfen Sie daher stets, ob ein Produkt das UL-Zeichen trägt.

UL gestattet die Weiterverwendung der im Online-Zertifizierungsverzeichnis enthaltenen Materialien unter den folgenden Bedingungen: 1. Alle Anleitungen, Baugruppen, Konstruktionen, Designs, Systeme und/oder Zertifizierungen (Dateien) müssen vollständig und auf nicht irreführende Weise ohne Manipulation der Daten (oder Zeichnungen) dargestellt werden. 2. Bei Weiterverwendung von Materialien muss der Vermerk „Aus dem Online-Zertifizierungsverzeichnis mit Genehmigung von UL nachgedruckt“ stets mit angegeben werden. Darüber hinaus muss das nachgedruckte Material einen Urheberrechtsvermerk in folgendem Format enthalten: "© 2019 UL LLC"