
product data sheet

item no. R1.190.1360.0

configurable control component SP-COP2-ENI-M-C DC 24



item no.	R1.190.1360.0
EAN	4049088563973
order unit	1 piece(s)

certificates / approvals

technical data

general

suitable for safety functions	yes
number of HW-interfaces industrial Ethernet	1
number of HW-interfaces USB	1
supporting protocol for EtherNet/IP	yes
supporting MODBUS protocol	yes
supporting protocol for PROFINET IO	yes
supporting TCP/IP protocol	yes
SIL according to IEC 61508	3
type of data transmission	serial
networkability	no
Erweiterbar	yes
programmable	yes
in-/outputs configurable	yes

connection data

type of electric connection	spring clamp connection
detachable clamps	yes

application

with automatic closing	yes
function contactless working protection installation	yes
function operating mode selection	yes
function emergency stop	yes
function contacter monitoring	yes
function restart blockage	yes
function acces control	yes

function affirm pushbutton	yes
function 2-hand switching	yes
on delay timer	yes
off delay timer	yes

output circuit

number of outputs	8
output current	4 A
short-circuit protection, outputs	yes
type of digital output	transistor
min. allowed output voltage	16.2 V
max. allowed output voltage	30 V
max. number of digital outputs, integrated	8

control circuit

min. rated DC voltage for controls	15.6 V
max. rated DC voltage for controls	30 V
number of inputs	16
input current with signal 1	2.3 mA
permitted voltage at input	30 V

supply circuit


nominal voltage DC	24 V
min. supply voltage	16.8 V
max. supply voltage	30 V


dimensions


depth	115 mm
width	45 mm
height	96 mm

technical drawing

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.







Teile-Nr. / Part-No.	Typ / Type
R1.190.1220.0	SP-COP2-EN-C
R1.190.1260.0	SP-COP2-EN-M-C
R1.190.1320.0	SP-COP2-ENI-C
R1.190.1360.0	SP-COP2-ENI-M-C

Weitere Angaben siehe KATALOG oder eKatalog.
Additional data see CATALOG or eCatalog.

www.wieland-electric.com
eshop.wieland-electric.com

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten.
Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance	CAD-Zeichnung, keine manuellen Änderungen CAD drawing, no manual modifications allowed	1. Verwendung: First Use:	Blatt: Sheet:

Index	Datum / Blatt Date / Sheet	Änderung / Revision	Maßstab/Scale	Werkstoff / Material	2023	Tag/Date	Name
					gezeichnet drawn	18.08.	Koetzner

Elektronische Freigabe
Electronic Release

Zeichnung Nr. / Drawing No.
T R1.190.1220.0 /01K

Maße in mm / Dimensions are in mm

Datei / File: 04158_B/R1.190.1120.0_01K.DCD

Ersatz für / Replacement for:

wieland

Type

Benennung / Title
Teilespezifikation / Component specification
Federkraftsteckblockklemme
samosPRO SP-COP2

01-QU-RD-31/21

2024-03-04 12:06:49 1.000